


<HLS-B>




动作特性
快动式




- OF_{max} 7.35N
- RF_{min} 0.98N
- PT_{max} 20°
- OT_{min} 50°
- MD_{max} 12°

<HLS-C>




动作特性
快动式




- OF_{max} 7.35N
- RF_{min} 0.98N
- PT_{max} 20°
- OT_{min} 50°
- MD_{max} 12°

<HLS-D>




动作特性
快动式




- OF_{max} 8.83N
- RF_{min} 1.47N
- PT_{max} 1.5mm
- OT_{min} 4mm
- MD_{max} 1mm

<HLS-H>



动作特性
快动式



- OF_{max} 8.83N
- RF_{min} 1.47N
- PT_{max} 1.5mm
- OT_{min} 4mm
- MD_{max} 1mm