




Standard Barrel Copper Lug

T&B Catalog Number:

UPC Number:
Status:
Description:

58163NP
78621091179
Active

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, 4/0 Flex Wire, 3/8" Bolt Size, Nickel Plated with Inspection Hole, Yellow 62

General

Material	Copper
Finish	Nickel Plated
Wire Size	4/0 Flex
Number of Studs	1
Stud Size	3/8
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Yellow
Die Code	62

Dimension Information

A (inches)	2.38
B (inches)	0.93
C (inches)	1.25
D (inches)	0.15
E (inches)	0.79
F (inches)	0.375

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	16.6 lbs. per 100

Application Support

Product Overview	Available on Website
------------------	----------------------

Notes

Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com