






Dimensions: mm (In.)





101-0163-EV



101-0263-EV



PCB Hole Layout

**Mechanical Specifications:**

- Temperature: -25°C ~ +70°C
- Operating force: 130 ±50gf
- Mechanical life: 500,000 cycles

Electrical Specifications:

- Rating: 50mA/12VDC
- Insulation resistance: >100MΩ @ 250VDC
- Dielectric Strength: 250VAC for 1 minute
- Contact resistance: <100MΩ
- Electrical life: 300,000 cycles

Material:

- Contact: phosphor bronze plated silver

Note:

- H: 124" (101-0163-EV), .152" (101-0263-EV)
- RoHS Compliant

Tactile Switches (Thru-Hole)
101-0163-EV, 101-0263-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0163-EV](#) [101-0263-EV](#)