


Customer No:



NOTE: All relevant materials are complied with RoHS directive .

|          |                                      |          |                                 |
|----------|--------------------------------------|----------|---------------------------------|
| 6        | PLASTO-VISCO-ELASTIC BODY            | 4        | M562                            |
| 5        | SCREW 3*6PWB                         | 4        | M805                            |
| 4        | METAL CASE, THICKNESS 0.8mm          | 1set     | M315                            |
|          | UL1061 26AWG INSULATOR, LENGTH 150mm | 40       | M541                            |
| 3        | MAIN HEART 3-9-4                     | 1        | M94                             |
|          | SCREW 4*12.5mm WITH PAD              | 1set     | M94                             |
|          | KNOB FOR A, B, C, D, SWITCH          | 1        | M94                             |
| 2        | STATOR                               | 1        | M348                            |
|          | PCB: RJ-45                           | 1        | M590                            |
|          | HEX-NUT WITH SCREW CAP 3*6mm         | 2set     | M95                             |
| 1        | RJ45 FEMALE, GOLD FLASH ON CONTACTS  | 5        | M22                             |
| No.      | DESCRIPTION                          | Q'TY     | Supplier                        |
| APPROVED |                                      |          | Cable Length Unless Other Spec. |
| CHECKED  | TIAN                                 |          | Tolerances:                     |
| DRAWING  | SUSAN                                |          | 0 ~200mm ±10mm                  |
|          |                                      |          | 201~1000mm ±20mm                |
|          |                                      |          | 1001 ~1500mm ±25mm              |
|          |                                      |          | 1501~2100mm ±30mm               |
|          |                                      |          | 2100mm± ±40mm                   |
| DATE     | 05/FEB/07                            | ITEM NO. | SB-384                          |
|          |                                      | UNIT:mm  |                                 |

| RJ45 F (I/O) | SWITCH | RJ45 F A&B&C&D |
|--------------|--------|----------------|
| 1            | 1      | 1              |
| 2            | 2      | 2              |
| 3            | 3      | 3              |
| 4            | 4      | 4              |
| 5            | 5      | 5              |
| 6            | 6      | 6              |
| 7            | 7      | 7              |
| 8            | 8      | 8              |