

Aluform Watertight Enclosures Product Drawings Last Updated 1/6/2006

Rose+Bopla Enclosures
7330 Executive Way
Frederick, MD 21704
301-696-9800
www.rose-bopla.com
customerservice@rose-bopla.com

Dimensional Drawings

Notes

Rose+Bopla's **Aluform Enclosures** are stylish, aluminum die-cast housings specifically designed for rugged electronic instrumentation applications.

Aluform Watertight Enclosures

Aluform enclosures feature an attractive beveled lid and are designed with a lower profile height than Rose+Bopla's standard 01 series housings. Internal mounting bosses in the base and lid provide convenience for component installation. New hinges, and one-piece external brackets are available as options.

An Aluform enclosure includes a powdercoat painted die-cast base and lid, captive stainless steel lid screws and a non-removable polyurethane gasket as the standard configuration. The unpainted version comes with a removable neoprene gasket.


Aluform Watertight Aluminum Enclosures—Painted

Part Number	Length (Inches/mm)	Width (Inches/mm)	Height (Inches/mm)	Weight	Drawing Page #
04080808 00	3.15 / 80	3.15 / 80	3.19 / 81	0.93 lbs	17-24
04081208 00	3.15 / 80	4.72 / 120	3.19 / 81	1.15 lbs	17-25
04101006 00	3.94 / 100	3.94 / 100	2.40 / 61	1.10 lbs	17-25
04101606 00	6.30 / 160	3.94 / 100	2.40 / 61	1.54 lbs	17-26
04102006 00	7.87 / 200	3.94 / 100	2.40 / 61	1.76 lbs	17-26
04121208 00	4.72 / 120	4.72 / 120	3.19 / 81	1.48 lbs	17-27
04121608 00	4.72 / 120	6.30 / 160	3.19 / 81	1.83 lbs	17-27
04141407 00	5.51 / 140	5.51 / 140	2.80 / 71	1.76 lbs	17-28
04141807 00	7.09 / 180	5.51 / 140	2.80 / 71	1.99 lbs	17-28
04142207 00	8.66 / 220	5.51 / 140	2.83 / 72	2.43 lbs	17-29
04161608 00	6.30 / 160	6.30 / 160	3.19 / 81	2.54 lbs	17-29
04162408 00	6.30 / 160	9.45 / 240	3.19 / 81	3.20 lbs	17-30
04202007 00	7.87 / 200	7.87 / 200	2.83 / 72	2.87 lbs	17-30
04202807 00	11.02 / 280	7.87 / 200	2.83 / 72	3.31 lbs	17-31

Aluform Watertight Aluminum Enclosures—Unpainted

Part Number	Length (Inches/mm)	Width (Inches/mm)	Height (Inches/mm)	Weight	Drawing Page #
04080808 85	3.15 / 80	3.15 / 80	3.19 / 81	0.93 lbs	17-24
04081208 85	3.15 / 80	4.72 / 120	3.19 / 81	1.15 lbs	17-25
04101006 85	3.94 / 100	3.94 / 100	2.40 / 61	1.10 lbs	17-25
04101606 85	6.30 / 160	3.94 / 100	2.40 / 61	1.54 lbs	17-26
04102006 85	7.87 / 200	3.94 / 100	2.40 / 61	1.76 lbs	17-26
04121208 85	4.72 / 120	4.72 / 120	3.19 / 81	1.48 lbs	17-27
04121608 85	4.72 / 120	6.30 / 160	3.19 / 81	1.83 lbs	17-27
04141407 85	5.51 / 140	5.51 / 140	2.80 / 71	1.76 lbs	17-28
04141807 85	7.09 / 180	5.51 / 140	2.80 / 71	1.99 lbs	17-28
04142207 85	8.66 / 220	5.51 / 140	2.83 / 72	2.43 lbs	17-29
04161608 85	6.30 / 160	6.30 / 160	3.19 / 81	2.54 lbs	17-29
04162408 85	6.30 / 160	9.45 / 240	3.19 / 81	3.20 lbs	17-30
04202007 85	7.87 / 200	7.87 / 200	2.83 / 72	2.87 lbs	17-30
04202807 85	11.02 / 280	7.87 / 200	2.83 / 72	3.31 lbs	17-31

Note: Dimensions are external. Metric is the primary dimension. Inch conversions and weights are for the user's convenience and are for reference only. Accessories shown on drawing page.



TECHNICAL DATA:

- Color: Powdercoated Version—Agate Gray similar to RAL 7038. Special colors are available. See paint specifications in the Technical Information Chapter.
Unpainted Version—Bare Aluminum.
- Material: Aluminum, AL Si 12. See Aluminum specification sheets in the Technical Information Chapter.
- Gasket Temperature Range:
Neoprene Gasket –40°F to +212°F
Polyurethane Foam Gasket –40°F to +194°F
Silicone Gasket –76°F to +266°F
RFI Gasket –40°F to +392°F
- Impact Resistance: >7Nm, EN50014
- Approvals: File #66473, UL 50, UL508
- Captive Lid Screws
- Protection Classifications:
NEMA Types: up to Nema 4X
IP 66, EN 60529




Standard Features

- 10093132 00 M4x20 Stainless steel captive combo head lid screws.
- 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (14" length). Non-Removable Polyurethane gasket for painted version.


Accessories

- 04000080 00 External Mounting Bars.
- 10011060 00 Mounting Plates.


Lid




View F



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



Base



Top




04081208 00/85

External Dimensions: L 80 x W 120 x H 81 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (20" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 04000080 00 External Mounting Bars. • 10011061 00 Mounting Plates. • 04000100 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 10 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket.




04101006 00/85

External Dimensions: L 100 x W 100 x H 61 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (14" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 10011031 00 Mounting Plates. • 10061041 00 Terminal Rail (TS 15). • 10061471 00 Terminal Rail (TS 35). • 04000100 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 10 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket. • 0430009 00 Enclosure holder 98mm wide.




04101606 00/85

External Dimensions: L 160 x W 100 x H 61 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (20" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 10011032 00 Mounting Plates. • 10061042 00 Terminal Rail (TS 15). • 10061472 00 Terminal Rail (TS 35). • 04000100 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 00 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket. • 04300009 00 Enclosure holder 98mm wide.




04102006 00/85

External Dimensions: L 200 x W 100 x H 61 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (22" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 10011033 00 Mounting Plates. • 10061043 00 Terminal Rail (TS 15). • 10061473 00 Terminal Rail (TS 35). • 04000100 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 00 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket. • 04300009 00 Enclosure holder 98mm wide.





04121208 00/85

External Dimensions: L 120 x W 160 x H 81 mm

Page 1-7


Standard Features

- 10093132 00 M4x20 Stainless steel captive combo head lid screws.
- 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (20" length). Non-Removable Polyurethane gasket for painted version.


Accessories

- 04000120 00 External Mounting Bars
- 10011062 00 Mounting Plates
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.



Lid



View F



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



04121608 00/85

External Dimensions: L 120 x W 160 x H 81 mm

Page 1-7


Standard Features

- 10093132 00 M4x20 Stainless steel captive combo head lid screws.
- 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (20" length). Non-Removable Polyurethane gasket for painted version.


Accessories

- 04000120 00 External Mounting Bars.
- 10011063 00 Mounting Plates.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.



Lid



View F



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688




04141407 00/85

External Dimensions: L 140 x W 140 x H 71 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (20" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 10011034 00 Mounting Plates. • 10061044 00 Terminal Rail (TS 15). • 10061474 00 Terminal Rail (TS 35). • 04000140 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 00 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket. • 04300014 00 Enclosure holder 138mm wide.




04141807 00/85

External Dimensions: L 180 x W 140 x H 71 mm

Page 1-7

Standard Features
• 10093132 00 M4x20 Stainless steel captive combo head lid screws. • 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (24" length). Non-Removable Polyurethane gasket for painted version.
Accessories
• 10011035 00 Mounting Plates. • 10061045 00 Terminal Rail (TS 15). • 10061475 00 Terminal Rail (TS 35). • 04000140 00 External Mounting Brackets. • 04000010 85 Unpainted External Hinges. • 04000010 00 Painted External Hinges. • 10082013 00 3.3mm Silicone gasket. • 10082022 00 3mm RFI gasket. • 04300014 00 Enclosure holder 138mm wide.





ROSE+BOPLA
ENCLOSURES

A PHOENIX MECANO COMPANY

04142207 00/85

External Dimensions: L220 x W140 x H71 mm


Page 1-7

Standard Features

- 10093132 00 M4x20 Stainless steel captive combo head lid screws.
- 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (28" length). Non-Removable Polyurethane gasket for painted version.

Accessories

- 10011036 00 Mounting Plates.
- 10061046 00 Terminal Rail (TS 15).
- 10061476 00 Terminal Rail (TS 35).
- 04000140 00 External Mounting Brackets.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.
- 04300014 00 Enclosure holder 138mm wide.



04161608 00/85

External Dimensions: L 160 x W 160 x H 81 mm


Page 1-7

Standard Features

- 10093132 00 M4x20 Stainless steel captive combo head lid screws.
- 10082003 00 Removable 3.3mm Neoprene Gasket for unpainted enclosures (24" length). Non-Removable Polyurethane gasket for painted version.

Accessories

- 04000160 00 External Mounting Bars.
- 10011064 00 Mounting Plates.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.



Dimensional Drawings

04162408 00/85

External Dimensions: L160 x W240 x H81 mm


Page 1-7

Standard Features

- **10093132 00** M4x20 Stainless steel captive combo head lid screws.
- **10082003 00** Removable 3.3mm Neoprene Gasket for unpainted enclosures (28" length). Non-Removable Polyurethane gasket for painted version.

Accessories

- 04000120 00 External Mounting Bars.
- 10011065 00 Mounting Plates.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.



04202007 00/85

External Dimensions: L200 x W200 x H71 mm


Page 1-7

Standard Features

- **10093132 00** M4x20 Stainless steel captive combo head lid screws.
- **10082003 00** Removable 3.3mm Neoprene Gasket for unpainted enclosures (30" length). Non-Removable Polyurethane gasket for painted version.

Accessories

- 10011037 00 Mounting Plates.
- 10061043 00 Terminal Rail (TS 15).
- 10061473 00 Terminal Rail (TS 35).
- 04000200 00 External Mounting Brackets.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.3mm Silicone gasket.
- 10082022 00 3mm RFI gasket.



Page 1-7

- 10011059 00 Mounting Plates.
- 10061048 00 Terminal Rail (TS 15).
- 10061481 00 Terminal Rail (TS 35).
- 04000200 00 External Mounting Brackets.
- 04000010 85 Unpainted External Hinges.
- 04000010 00 Painted External Hinges.
- 10082013 00 3.2mm Silicone gasket.
- 10082022 00 3mm RFI gasket.

