

FILTERS

HIGH PASS

8 PIN - RELAY HEADER

Low Cost



Fc (MHz) LOSS = 3 dB (Nom)	PASSBAND LOSS < 1 dB (MHz)	STOP BAND FREQUENCY (MHz)			PASS BAND V SWR (TYP)	PACKAGE	PIN-OUT (See Below)	MODEL
		>35 dB	>23 dB	>20 dB				
10	10.7-50	5	6	7	1.70:1	102	1	FHP-10
20	21.4-100	10	13	15	1.70:1	102	1	FHP-20
27	30-150	14	17	20	1.70:1	102	1	FHP-27
45	50-250	23	29	34	1.70:1	102	1	FHP-45
55	60-300	28	35	41	1.70:1	102	1	FHP-55
64	70-300	32	40	48	1.70:1	102	1	FHP-64
127	140-630	65	80	95	1.70:1	102	1	FHP-127
182	200-850	90	110	135	1.70:1	102	1	FHP-182
270	300-1200	135	170	200	1.70:1	102	1	FHP-270
410	450-1400	205	255	305	1.70:1	102	1	FHP-410
545	600-1600	225	320	410	1.70:1	102	1	FHP-545
680	750-1900	340	425	510	1.70:1	102	1	FHP-680
795	875-2000	400	500	600	1.70:1	102	1	FHP-795

NOTE: All units meet or exceed applicable MIL-F-18327.
For other frequencies and impedances please contact us.
Impedance is 50 Ohms for all models.

For pin location and package outline drawings, see backpages.

PIN-OUT TABLE

INPUT	OUTPUT	CASE GROUND
1	8	All Other