



Wiha Long Life Precision Series



260 Slotted Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.



Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
260 08	.80	1/32	40	1.6	0.16	.01	120	4.7	.02	10
260 10	1.0	.039	40	1.6	0.18	.01	120	4.7	.02	10
260 12	1.2	3/64	40	1.6	0.20	.01	120	4.7	.02	10
260 15	1.5	1/16	40	1.6	0.25	.01	120	4.7	.02	10
260 18	1.8	.070	40	1.6	0.30	.01	120	4.7	.02	10
260 20	2.0	5/64	40	1.6	0.40	.02	120	4.7	.02	10
260 22	2.0	5/64	50	2.0	0.40	.02	145	5.7	.02	10
260 23	2.0	5/64	100	3.9	0.40	.02	180	7.1	.03	10
260 25	2.5	3/32	50	2.0	0.40	.02	145	5.7	.03	10
260 27	2.5	3/32	100	3.9	0.40	.02	195	7.7	.03	10
260 28	2.5	3/32	150	6.0	0.40	.02	245	9.6	.04	10
260 30	3.0	1/8	50	2.0	0.50	.02	145	5.7	.03	10
260 32	3.0	1/8	60	2.4	0.50	.02	170	6.7	.04	10
260 33	3.0	1/8	100	3.9	0.50	.02	210	8.3	.04	10
260 34	3.0	1/8	150	5.9	0.50	.02	260	10.2	.05	10
260 35	3.5	9/64	60	2.4	0.60	.02	170	6.7	.05	10
260 40	4.0	5/32	60	2.4	0.80	.03	170	6.7	.05	10
260 41	4.0	5/32	100	3.9	0.80	.03	210	8.3	.06	10
260 42	4.0	5/32	150	5.9	0.80	.03	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



260 90 Set 6 Pcs. Slotted

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.



Item No.		mm	mm	lbs.
260 90	260 15	1.5	40	.27
	260 20	2.0	40	
	260 25	2.5	50	
	260 30	3.0	50	
	260 35	3.5	60	
	260 40	4.0	60	



260 99 Set 8 Pcs. Slotted In Rugged Canvas Pouch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In storage pouch



Item No.		mm	mm		mm	mm	lbs.
260 99	260 10	1.0	40	260 25	2.5	50	.54
	260 12	1.2	40	260 30	3.0	50	
	260 15	1.5	40	260 35	3.5	60	
	260 20	2.0	40	260 40	4.0	60	

Rotating cap

for precise turning and control with fingertip

Precision handle

high quality plastic, cadmium free

Molded on tapered handle

allows rapid rotation

High performance blades

chrome-vanadium-molybdenum steel, Hard chrome finished

Tip

precision ground for exact fit, hard chromed non-slip surface



[See Carded Precision Screwdrivers On Page 147](#)