




1 AMP



3 AMP



6 AMP




SF 1070	Rated Current A	Leakage Current @ 250V 50Hz	Inductance L1 mH	L2 mH	Connections Input	Output	Approvals		
SF 1070-1/01	1	0.2mA	4.5	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
SF 1070-1/03	1	0.2mA	4.5	0.3	IEC 320	Solder Tag	■	■	■
SF 1070-3/01	3	0.2mA	1.2	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
SF 1070-3/03	3	0.2mA	1.2	0.3	IEC 320	Solder Tag	■	■	■
SF 1070-6/01	6	0.2mA	0.5	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
SF 1070-6/03	6	0.2mA	0.5	0.3	IEC 320	Solder Tag	■	■	■

Temperature Range: -25°C to +85°C
Operating Voltage: 250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L+N to ground, 2700Vdc, 2 seconds

■ Approved
 □ Submitted for Approval

DIMENSIONS

All dimensions are nominal and in mm



IEC 950 (EN 60950) Applications

CIRCUIT DIAGRAM

