

KSC9 Series SMD Sealed Tact Switch for Adjustable Height

NEW!

Features/Benefits

- SMD switch
- Adjustable height with buttons
- Overload resistance
- Tape & reel
- IP 67

Typical Applications

- Industrial electronics
- Network equipment
- Telecommunications



B

Tactile Switches

Specification

FUNCTION: momentary action
CONTACT ARRANGEMENT: 1 make contact = SPST, N.O.
TERMINALS: J bend or Gullwing type for SMT
CONTACT ARRANGEMENT: 1 make contact = SPST, N.O.

Mechanical

Type	Force (N)	Operating Life (operations)	Travel (mm)
KSC921J LFS	1.7 ± 0.5	300,000	0.4 ± 0.2
KSC931J LFS	2.55 ± 0.65	300,000	0.4 ± 0.2
KSC941J LFS	3.4 ± 0.85	300,000	0.4 ± 0.2

BUTTON INSETION OVERLOAD: 40N

BUTTON RETENTION FORCE: 7N min between -40°C/+85°C

Electrical

	Silver	Gold
MAXIMUM POWER:	1 VA	0.2 VA
MAXIMUM VOLTAGE:	32 VDC	32 VDC
MINIMUM VOLTAGE:	20 mV	20 mV
MAXIMUM CURRENT:	50 mA	10 mA
MINIMUM CURRENT:	1 mA	1 mA

DIELECTRIC STRENGTH (50 Hz, 1 min.): > 250 Vrms

CONTACT RESISTANCE: < 100 mΩ

INSULATION RESISTANCE (100 V initial stage): > 10⁹ Ω

BOUNCE TIME: < 1 ms

Environmental

	Silver	Gold
OPERATING TEMPERATURE:	-40°C to 85°C	-40°C to 125°C
STORAGE TEMPERATURE:	-55°C to 85°C	-55°C to 125°C

Process

SOLDERING: Depending on the application, this component is suited to the following methods:

- Cleaning according to typical washing processes.
 - Infrared Reflow Soldering in accordance with IEC 61760-1.
- MSL level: 2a

Packaging

In reels of 750 pieces.

Dimensions of reels according to EIA RS481 or IEC 2863.


External diameter 330 mm ± 2 mm.

NOTE: This product is designed and manufactured for general electronic devices. For systems where reliability and safety are required, please contact your sales representative to secure product integration and function to secure usage.

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

For any part number different from those listed above, please consult your local representative.



29 May 12

B-38

Dimensions are shown: mm
Specifications and dimensions subject to change

www.ck-components.com


NEW!

KSC9 Series SMD Sealed Tact Switch for Adjustable Height




B

Tactile Switches




TERMINATION

J J BEND



G GULLWING



29 May 12

NEW!

Technical drawing of a mechanical part, showing a top view and a side view.

The top view is a circle with a diameter of $\varnothing 6.35$. It features a central rectangular hole and four semi-circular cutouts.

The side view is a rectangle with a height of 10.2 ± 0.1 mm and a width of $\varnothing 6$ mm. The top edge is rounded with a radius of $R0.25$.

Tactile Switches

15.4±0.4

SWITCH WITH CAP



Direction of feed

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Components:

[BTN KSC9 20](#) [BTN KSC9 40](#) [BTN KSC9 80](#) [BTN KSC9 90](#) [KSC921G LFS](#) [KSC921J LFS](#) [KSC931G LFS](#)
[KSC931J LFS](#) [KSC941G LFS](#) [KSC941J LFS](#)