







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. DIELECTRIC STRENGTH: 1kV RMS min. at sea level
6. ELECTRICAL LIFE: 10,000 make-and-break cycles
at full load.
7. MATERIALS:



RECOMMENDED PANEL LAYOUT



CIRCUIT: SP (45°/45°/90° INDEXING)
CONTACT CONFIGURATION

SWITCH FUNCTION				
CONNECTED TERMINAL #				
POS. 1	POS. 2	POS. 3	POS. 4	POS. 5
6-7	7-8	8-1	NONE	1-3

LEGEND

- = Detent Positions (45° or 90°)
- ⊙ = Key pull possible in these positions

A	13055	RELEASED FOR PRODUCTION	4/17/03 AR
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			

E-SWITCH®				
TITLE				
K0130V-A126				
SCALE	DATE	DR	DWG	REV
1:1	4/17/03	AR	K200231	A