


Specifications:

| | |
|-------------------------|-----------------------------------|
| Sound level Category | Loud Sound Level |
| Mode of Operation | Continuous tone |
| Mounting | Panel (see note) |
| Voltage Rating | 6 - 16 Vdc |
| Frequency | 2900 Hz \pm 500 Hz |
| Loudness (Min. Voltage) | 80 dB(A) min. @ 2 FT and 6 Vdc |
| Loudness (Max Voltage) | 95 dB(A) min. @ 2 FT and 16 Vdc |
| Current Draw | 6 mA Max @ 6 Vdc |
| Current Draw | 22 mA Max @ 16 Vdc |
| Storage Temperature | -40°C to +85°C |
| Operating Temperature | -30°C to +65°C |
| Weight (Typical) | 1.5 oz (42 g) |
| Housing | 6/6 Nylon, and Color Black |
| Options | For other options contact factory |

Dimensions: Inches (mm)**UL Recognized** 

NOTE: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SC616NL](#)