

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [90835-0038](#)
Status: **Active**
Overview: [RAST 5 Connector System](#)
Description: 5.00mm Pitch Appli-Mate RAST 5 IDT Connector System Female Receptacle, 16A, 2 Circuit, Purple Red, Coding Keys 01c, d20, Latch Position 1/2, Position Keys 2b

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family IDT and Solder Connectors
Series [90835](#)
Comments Female Indirect Receptacle Reference K15
Crimp Quality Equipment Yes
Overview [RAST 5 Connector System](#)
Product Name RAST 5
UPC 800753651029
Use With RAST standard interface


Physical

Circuits (Loaded) 2
Circuits (maximum) 2
Color - Resin Natural
Durability (mating cycles max) 10
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Silver
Material - Plating Termination Silver
Material - Resin Nylon
Net Weight 3.044/g
Number of Rows 1
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 5.00mm
Pitch - Termination Interface 5.00mm
Plating min - Mating 2.032µm
Plating min - Termination 0.102µm
Polarized to Mating Part Yes
Stackable Yes
Temperature Range - Operating -20C to +120C
Termination Interface: Style IDT or Pierce
Wire Size AWG 16 Stranded, 18

Electrical

Current - Maximum per Contact 16A
Voltage - Maximum 250V AC

Material Info



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[90835Series](#)

Mates With

[90858 Header](#), [90879 Header](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Manual Arbor Press, RAST 5.0	0622017500
RAST 5.0 Power Semi-Automatic Terminator Machine for 12 and 16 AMP	0623006100

Reference - Drawing Numbers

Sales Drawing

onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

This document was generated on 11/27/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com