






**HEADER RIGHT ANGLE SOLDER PIN,  
1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 5 MM / 0.197 IN 100%  
PROTECTED AGAINST MISMATING**



**HEADER RIGHT ANGLE SOLDER PIN,  
1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 5 MM / 0.197 IN 100%  
PROTECTED AGAINST MISMATING  
721-432/001-000 TO 721-450/001-000**

|                                                      |                                                                              |
|------------------------------------------------------|------------------------------------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 721-445/001-000                                                              |
| Measured voltage (Measured voltage / V)              | 320                                                                          |
| Measured shock voltage (Measured shock voltage / kV) | 4                                                                            |
| Pollution degree (Pollution degree)                  | 2                                                                            |
| Current intensity (Current intensity / A)            | 12                                                                           |
| RM (PIN SPACING / mm)                                | 5                                                                            |
| P (NO. OF POLES)                                     | 15                                                                           |
| Height (Height / mm)                                 | 11.4                                                                         |
| Width (Width / mm)                                   | 78.8                                                                         |
| Depth (Depth / mm)                                   | 12                                                                           |
| COLOR (COLOR)                                        | lichtgrau                                                                    |
| Comment (Comment)                                    | A = (No. of poles x Pin Spacing) + 3,2 mm   B<br>= A + 5 mm   C = B + 7,4 mm |
| Dimensions (Dimensions)                              | 1,4 +0,1 mm                                                                  |