

521 SERIES NEON LAMPS

T-2 MIDGET FLANGE BASE

PART NO.	LAMP NO.	VOLTS	CURRENT	OHMS	WATTS	LIFE HOURS
521-9047	C7A (NE-2D)	105–125 AC/DC	.70	100K	1/4	25,000
521-9048*	C9A (NE-2J)	110–125 AC	1.9	30K	1/4	25,000

T-2 MIDGET
FLANGE BASE
NEON LAMP



T-3 1/4 MINIATURE BAYONET BASE

PART NO.	LAMP NO.	VOLTS	CURRENT	OHMS	WATTS	LIFE HOURS
521-9053	B1A (NE-51)	105–125 AC-DC	.3	220K	1/4	25,000
521-9054*	B2A (NE-51H)	110–125 AC†	1.2	47K	1/4	25,000

T-3 1/4
MINIATURE
BAYONET BASE
NEON LAMP



T-4 1/2 CANDELABRA SCREW BASE

PART NO.	LAMP NO.	VOLTS	CURRENT	OHMS	WATTS	LIFE HOURS
521-9051	B7A (NE-45)	105–125	2.0	30K	1/4	5,000
	F4A (NE-58)	210–250	2.0	100K	1/3	5,000

T-4 1/2
CANDELABRA
SCREW BASE
NEON LAMP



521 SERIES INCANDESCENT LAMPS

T-1 3/4 MIDGET FLANGE BASE

PART NO.	LAMP NO.	VOLTS	AMPS	MSCD	LIFE HOURS
–	331	1.35	.06	.006	3,000
–	338	2.7	.06	.04	6,000
–	7332	5.0*	.06	.05	30,000
521-0328	328	6.0*	.20	.63	1,000
521-0345	345	6.0*	.04	.03	10,000
–	349	6.3*	.20	.55	5,000
–	380	6.3*	.04	.02	20,000
–	381	6.3*	.20	.40	20,000
–	344	10.0*	.014	.002	50,000
–	367	10.0*	.04	.08	10,000
–	394	12.0*	.04	.10	10,000
521-0330	330	14.0*	.08	.50	2,500
521-0382	382	14.0*	.08	.30	15,000
521-0370	370	18.0*	.04	.15	10,000
521-0327	327	28.0*	.04	.34	4,000
521-0387	387	28.0*	.04	.30	7,000

T-1 3/4 MIDGET
FLANGE BASE
INCANDESCENT LAMP



* Also available in T-1 3/4
multichip Based LED versions.
See page 38 for information.

T-2 TELEPHONE SLIDE BASE (PSB TYPE)

PART NO.	LAMP NO.	VOLTS	AMPS	MSCD	LIFE HOURS
–	6PSB	6	.140	550	20,000
–	12PSB	12	.170	2000	12,000
–	24PSB	24	.073	3000	10,000
–	28PSB	28	.040	1600	5,000
–	48PSB	48	.053	1800	7,500
–	60PSB	60	.050	.05	7,500
–	120PSB	120	.025	–	10,000

T-2 TELEPHONE
SLIDE BASE
INCANDESCENT LAMP



* High Brightness

† For 220–250 AC-DC Operation, Ohms 150K, Watts 1/3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[521-0382](#) [521-0370](#) [521-0330](#) [521-0327](#) [521-0328](#) [521-0387](#) [521-0345](#)