



32" Class Viera® U22 Series 1080p LCD

Model number: TC-L32U22

7 Reviews

Print this | Share this

Product no longer available for purchase.

32" Class Viera® U22 Series 1080p LCD (31.5" Diagonal)

- IPS Panel
- VIERA Image Viewer™
- VIERA Link™
- ENERGY STAR Qualified

Online Order Assistance

- [Track your order](#)
- [Print your invoice](#)
- [Read our shipping FAQs](#)
- [Register your product](#)

Accessories

- [Find accessories for your product](#)

Contact Us

- [Live Chat](#)
- [Phone](#)
- [Email](#)
- [Mail](#)
- [International Support](#)

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Accessories	Drivers & Downloads
Model Type				LCD		
Series				U22		
Model Year				2010		
VIDEO						
Screen Size				32" Class (31.5" diagonal)		
Viewing Angle				178°		
Aspect Ratio				16:9		
Native Resolution (Number of Pixels)				2,073,600 (1,920 x 1,080)		
HDTV Display Capability (1080p, 1080i, 720p)				Yes		
EDTV Display Capability (480p)				Yes		
Aspect Control				480i/p: Full, Just, 4:3, Zoom 1080i/p: Full, H-Fill, Just, 4:3, Zoom		
Panel				IPS 1080p (WSXGA)		
Filter				Fine Black Panel		
Backlight				CCFL		
Progressive Scan				Yes		
24p Playback(2:3)				Yes		
Intelligent Scene Controller				Yes		
Motion Focus Technology				No		
Contrast (Dynamic)				20,000:1		
120 Hz				No		
24p Smooth Film				No		
AUDIO						
Speakers				Full-range x 2 (L, R)		
Number of Speakers				2		
Audio Output				20 W (10% THD)		
Surround Sound				Yes		
INPUTS & JACKS						
Integrated ATSC Tuner				Yes		
VIERA Image Viewer™				Y (JPEG playback)		
HDMI Input				3 (1 side)		
Analog Audio Input (for HDMI)				Yes		
Composite Video Input				2 (1 side)		
Audio Input (for Video)				2 (1 side)		
PC Input				1		
Component Video Inputs (Y, PB, PR)				1		
Audio Input (for Component Video)				1		
Digital Audio Output				1 (5.1 ch)		
HDMI Input-Support Feature				Audio Return Channel (Input 1)		
CONVENIENCE						
VIERA Link™				Yes		
Universal Dock for iPod				No		
VIERA® Tools				Yes		
Game Mode				No		
Clean Touch Bezel				No		
Built-In Closed Caption Decoder				Yes		
Trilingual Menu				English/Spanish/French		
Sleep Off-Timers and Programable Timer				Yes (5 programs)		
GENERAL						
Power Supply				AC 110 - 127 V, 60 Hz		
Rated Power Consumption				102 W		
Standby Power Consumption				0.3 W		
On Mode Average Power Consumption				(51.6 W)		
Energy Star				Yes		
Receiving System				ATSC/QAM/NTSC		
Swivel Angle				No		
Tilt Angle				No		
VESA Compatible				Yes		
Optional Wall-mounting Bracket				TY-WK3L2RW		
SPECIFICATIONS						
Dimensions (H x W x D) with Stand				21.7" x 31.5" x 8.6"		
Dimensions (H x W x D) without Stand				20.2" x 31.5" x 3.3"		
Weight (lbs.) w/Stand				24.3 lbs.		
Weight (lbs.) without Stand				21.0 lbs.		
Carton Dimensions				23.7" x 40.6" x 7.6"		
Gross Weight [lbs (kg)]				30.9 lbs		