


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS	MAX. SCREW SIZE
MBMS-S10Y	.123 (55.8)	MINIATURE INTERMEDIATE STANDARD	#10 (M5)

NOTES:

- NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 2. MATERIAL: ALUMINUM ALLOY - 3003-H14 (HALF HARD, TEMPER).
 3. FINISH: RoHS COMPLIANT TCP COATING
CORROSION RESISTANCE: 168 HRS SALT SPRAY PER ASTM-B-117

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS



CORP.

TINLEY PARK, ILLINOIS

MBMS-S10Y
METAL MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED.

ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE	7/27/06
------	---------

SEE NOTE 2.3

DRAWING NO.
GB02391 W

DWG
A
SIZE

R	7/27/06	JAD		INITIAL RELEASE	GB0239LW	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	