







Jack

161-3503

KOBI CONN

Jack



Dimensions: mm (In.)

[Tolerance ± 0.3 (.012) except where noted.]

SOLDER PROCESS

Solder Temperature: 260°C Max. for 5 Seconds

ELECTRICAL SPECIFICATIONS

Rating: 12VDC 0.5A

Contact Resistance: 30mΩ Max.

Insulation Resistance: 50MΩ Min. @ 500VDC

Withstand Voltage: 500VAC for 1 Minute

MATERIALS

Type: PC Mount 3.5mm Stereo Phone w/ Switch

Housing: Polycarbonate Resin

Switch Terminal: Silver Plated Brass

Fixed Terminals: Silver Plated Brass

Ground Terminal: Silver Plated Phosphor Bronze

Tip Springs: Silver Plated Steel

Date Last Revised: 08-20-04

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300124

161-3503

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3503](#)