


Capacitor, aluminum, 220 uF, +/-20% Tol, -40/+105C, 35VDC@105C



Note: '()' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
D	10	+/-0.5
L	12	+1.5/-0
S	5	+/-0.5
LLPos	20	MIN
LLNeg	15	MIN
F	0.6	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	4000

General Information	
Supplier:	KEMET
Application:	105C LowZ
Part Type Description:	Low ESR Single Ended Aluminum Electrolytic
Style:	Single Ended
Lead Type:	Straight

Specifications	
Capacitance:	220 uF
Tolerance:	+/-20%
Rated Temperature:	105C
Voltage:	35VDC
VDC Surge:	44VDC
Life @ rated temp:	2000 Hrs
RoHS:	Yes
Temperature Range:	-40/+105C
Leakage Current:	77 uA
Leakage Condition:	2min/20c
Dissipation Factor:	10%
Impedance @ 100kHz:	69 mOhm
Impedance Ratio -40C:	4.0
Current/Ripple Current:	800 mA (100kHz 105C)