

Anti-corrosive polycarbonate luminaires for T8 and T5 lamps

- High-impact and corrosion-resistant light grey, injection moulded polycarbonate body
- Clear prismatic polycarbonate cover
- Body and cover flame-retardant
- Smooth easy-clean lines
- Snug-fit polycarbonate cover clips (stainless steel option see page 42)
- Fast installation via external stainless-steel brackets preserves IP rating
- Optional narrow distribution reflector for rack lighting applications
- Complies with M.O.D. JSP482 Chapter 8 Document for 'Category C' areas



IP65    

Range

NOMINAL SIZE (mm)	LAMP	CAT. No.	LENGTH (mm)	FIXINGS	APPROX. kg	STANDARD CIRCUIT	EMERGENCY CIRCUIT	AUTOTEST CIRCUIT
T8 LAMP VERSIONS								
1200	1 x 36W T8	TP 10411	1270	920mm centres	3.0	E-J-S	E-J	-
	2 x 36W T8	TP 10412			4.0	E-J-S	J	-
1500	1 x 58W T8	TP 10413	1570	1150mm centres	4.2	E-J-S	E-J	-
	2 x 58W T8	TP 10414			5.5	E-J-S	J	-
T5 LAMP VERSIONS								
1200	1 x 28W T5	TP 12075	1270	920mm centres	3.0	J	J	J
	2 x 28W T5	TP 13400			4.0	J	J	J
1500	1 x 35W T5	TP 11795	1570	1150mm centres	4.2	J	J	J
	2 x 35W T5	TP 11796			5.5	J	J	J
1500	1 x 49W T5	TP 11797	1570	1150mm centres	4.2	J	J	J
	2 x 49W T5	TP 11798			5.5	J	-	-

FACTORY FITTED THROUGH WIRING - add 'TW' after catalogue number eg. **TP 10411TW**

CIRCUIT - add suffix required:

E - electronic start **J** - high frequency **S** - switch start e.g. **TP 10411E** etc.

EMERGENCY VERSION - prefix catalogue number with 'ETP':

AUTOTEST VERSION - prefix catalogue number with 'TTP':

Emergency and AutoTest versions add 0.7kg to weights listed.

LAMPS MUST BE ORDERED SEPARATELY, SEE PAGE 284 FOR DETAILS



DIRECT

Pair of stainless steel brackets supplied. Provides clearance for thermal expansion and fixing.



PENDANT


Pair of steel spring loops supplied.



Accessories

DESCRIPTION	CAT. No.	APPROX. kg
Narrow distribution reflector (Single 58W T8)	TP 10415	0.15
Narrow distribution reflector (Twin 58W T8)	TP 10416	0.5
Narrow distribution reflector (Single 35/49W T5)	TP 11836	0.15
Narrow distribution reflector (Twin 35/49W T5)	TP 11835	0.5
IP65 20mm weatherproof compression gland kit with sealing washers	IK 6389	0.02
Stainless steel adjustable bracket (Short) - two per pack	IK 10419	0.13
Stainless steel adjustable bracket (148mm long) - two per pack	IK 10420	0.24
Stainless steel suspension hook - two per pack	IK 10421	0.05
Stainless steel cover clip - eight required per 1200mm body - ten required per 1500mm body	TP 10541	-


Through wiring kits are available - details upon request



Photometric Guide

1 x 28W


D.L.O.R. 83% U.L.O.R. 13%



FACTOR: 1 x 35W = 0.98
1 x 49W = 0.99

2 x 28W

D.L.O.R. 82% U.L.O.R. 10%



FACTOR: 2 x 35W = 0.98
2 x 49W = 0.94

