# SUB-MINI & MINIATURE TOGGLES

Fig. 1

Fig. 2

Fig. 3

Fig. 4

Fig. 5

Fig. 6

Fig. 7

Fig. 8

Fig. 9

Fig. 10

Fig. 11

Fig. 12

## Sub-Miniature Toggles

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 35-000 | 35-000-BU | 1 | On Off | SPST | 3A | 1.5 | Bat | BCP | 0.220 | 0.195 | Solder | 2 N, LR, LW | 267-A |
| 35-001 | 35-001-BU | 2 | On On | SPDT | 3A | 1.5 | Bat | BCP | 0.220 | 0.195 | Solder | 2 N, LR, LW | 267-A |
| 35-002 | 35-002-BU | 3 | On On | DPDT | 3A | 1.5 | Bat | BCP | 0.220 | 0.195 | Solder | 2 N, LR, LW | 267-A |

## Miniature Toggles

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 35-003 | 35-003-BU | 2 | On (On) | SPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-004 | 35-004-BU | 2 | On On | SPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-005 | 35-005-BU | 2 | On Off On | SPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-006 | 35-006-BU | 4 | On Off | SPST | 5 | 2 | Bat with Boot | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-007 | 35-007-BU | 2 | On Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-008 | 35-008-BU | 2 | (On) Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-B |
| 35-009 | 35-009-BU | 5 | On On On | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-C |
| 35-010 | 35-010-BU | 6 | On On | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-012 | 35-012-BU | 6 | On Off On | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-014 | 35-014-BU | 6 | On (On) | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-016 | 35-016-BU | 6 | On Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-018 | 35-018-BU | 6 | (On) Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-024 | 35-024-BU | 7 | On On | 3PDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-D |
| 35-026 | 35-026-BU | 7 | On Off On | 3PDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-D |
| 35-036 | 35-036-BU | 8 | On On | 4PDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| 35-038 | 35-038-BU | 8 | On Off On | 4PDT | 5 | 2 | Bat | BCP | 0.350 | 0.250 | Solder | 2 N, LR, LW | 267-E |
| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | AMPS 125VAC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
| 35-053 | 35-053-BU | 9 | On On | SPDT | 5 | 2 | Flat Lever | Metal | 0.364 | 0.250 | PCB | 2 N, LR, LW | 267-F |
| 35-055 | 35-055-BU | 9 | On Off On | SPDT | 5 | 2 | Flat Lever | Metal | 0.364 | 0.250 | PCB | 2 N, LR, LW | 267-F |
| 35-057 | 35-057-BU | 10 | On On | DPDT | 5 | 2 | Flat Lever | Metal | 0.364 | 0.250 | PCB | 2 N, LR, LW | 267-F |
| 35-059 | 35-059-BU | 10 | On Off On | DPDT | 5 | 2 | Flat Lever | Metal | 0.364 | 0.250 | PCB | 2 N, LR, LW | 267-F |
| 35-070 | 35-070-BU | 11 | On On | SPDT | 6 | 3 | Paddle | Polyamide | 0.452 | 0.500 | Solder/QC | N, KN | 267-G |
| 35-071 | 35-071-BU | 11 | On Off On | SPDT | 6 | 3 | Paddle | Polyamide | 0.452 | 0.500 | Solder/QC | N, KN | 267-G |
| 35-072 | 35-072-BU | 12 | On On | DPDT | 6 | 3 | Paddle | Polyamide | 0.452 | 0.500 | Solder/QC | N, KN | 267-G |
| 35-073 | 35-073-BU | 12 | On Off On | DPDT | 6 | 3 | Paddle | Polyamide | 0.452 | 0.500 | Solder/QC | N, KN | 267-G |

Notes: (On)=Momentary On
BCP=Brass Chrome Plate
KN=Knurled Nut
LR=Lock Ring
LW= Lock Washer
N=Nut(s)
PCB=Printed Circuit Board
QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.





Phone (815)316-9080•Fax (815)316-9081

All quantities are single; BU's are packages of 10 Unless otherwise noted.

**A**




**B**




**C**




**D**




**E**




**F**




**G**






All quantities are single; BU's are packages of 10 Unless otherwise noted.

# MINIATURE TOGGLES (Cont.)

Fig. 1

Fig. 2

Fig. 3

Fig. 4

## Miniature Toggles with Printed Circuit Board Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **35-087** | **35-087-BU** | 1 | On On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-A |
| **35-069** | **35-069-BU** | 1 | On (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-A |
| **35-074** | **35-074-BU** | 1 | On Off On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-A |
| **35-075** | **35-075-BU** | 1 | On Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-A |
| **35-077** | **35-077-BU** | 1 | (On) Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-A |
| **35-079** | **35-079-BU** | 2 | On On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-B |
| **35-081** | **35-081-BU** | 2 | On (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-B |
| **35-082** | **35-082-BU** | 2 | On Off On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-B |
| **35-083** | **35-083-BU** | 2 | On Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-B |
| **35-085** | | 2 | (On) Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB | 2 N, LR, LW | 269-B |

## Miniature Toggles with Printed Circuit Board with Integral Bracket Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **35-088** | **35-088-BU** | 3 | On On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-C |
| **35-089** | **35-089-BU** | 3 | On (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-C |
| **35-091** | **35-091-BU** | 3 | On Off On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-C |
| **35-093** | **35-093-BU** | 3 | On Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-C |
| **35-095** | **35-095-BU** | 3 | (On) Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-C |
| **35-096** | **35-096-BU** | 4 | On On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-D |
| **35-097** | **35-097-BU** | 4 | On (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-D |
| **35-098** | **35-098-BU** | 4 | On Off On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-D |
| **35-099** | **35-099-BU** | 4 | On Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-D |
| **35-101** | **35-101-BU** | 4 | (On) Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB† | 269-D |

Notes: (On)=Momentary On
BCP=Brass Chrome Plate
LW= Lock Washer
N=Nut(s)
LR=Lock Ring
PCB=Printed Circuit Board
PCB†=Printed Circuit Board with Integral Bracket

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.





Phone (815)316-9080•Fax (815)316-9081

All quantities are single; BU's are packages of 10 Unless otherwise noted.

## A




## B




## C




## D








All quantities are single; BU's are packages of 10 Unless otherwise noted.

## MINIATURE TOGGLES (Cont.)

Fig. 1

Fig. 2

Fig. 3

Fig. 4

### Miniature Toggles with Printed Circuit Board Right Angle Vertical Mount Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 35-102 | 35-102-BU | 1 | On On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-A |
| 35-103 | 35-103-BU | 1 | On (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-A |
| 35-104 | 35-104-BU | 1 | On Off On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-A |
| 35-105 | 35-105-BU | 1 | On Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-A |
| 35-106 | 35-106-BU | 1 | (On) Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-A |
| 35-107 | 35-107-BU | 2 | On On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-B |
| 35-108 | 35-108-BU | 2 | On (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-B |
| 35-109 | 35-109-BU | 2 | On Off On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-B |
| 35-111 | 35-111-BU | 2 | On Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-B |
| 35-113 | 35-113-BU | 2 | (On) Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB†† | 271-B |

### Miniature Toggles with Printed Circuit Board Right Angle Horizontal Mount Terminals

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | 125VAC/ 28VDC | AMPS 250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 35-115 | 35-115-BU | 3 | On On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-C |
| 35-121 | 35-121-BU | 3 | On (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-C |
| 35-122 | 35-122-BU | 3 | On Off On | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-C |
| 35-123 | 35-123-BU | 3 | On Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-C |
| 35-125 | 35-125-BU | 3 | (On) Off (On) | SPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-C |
| 35-127 | 35-127-BU | 4 | On On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-D |
| 35-129 | 35-129-BU | 4 | On (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-D |
| 35-131 | 35-131-BU | 4 | On Off On | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-D |
| 35-133 | 35-133-BU | 4 | On Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-D |
| 35-135 | 35-135-BU | 4 | (On) Off (On) | DPDT | 5 | 2 | Bat | BCP | 0.350″ | 0.250″ | PCB††† | 271-D |

Notes: (On)=Momentary On
BCP=Brass Chrome Plate

KN=Knurled Nut
LR=Lock Ring

LW= Lock Washer
N=Nut(s)

PCB=Printed Circuit Board
PCB†=Printed Circuit Board with Integral Bracket
QC=Quick Connect
PCB††=Printed Circuit Board Right Angle Vertical Mount
PCB†††=Printed Circuit Board Right Angle Horizontal Mount

Fig. 5

Fig. 6

Fig. 7

Fig. 8

| Retail Part No. | Bulk Part No. | Figure No. | Circuit Function | Poles/ Throws | AMPS 125VAC | AMPS 250VAC | AMPS 12VDC | HP 125-250VAC | Actuator Style | Color | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 35-090 | 35-090-BU | 5 | On Off | SPST | | | 16 | | Paddle* | Red | 0.342 | 0.500 | QC .250″ | N, LN | 271-E |
| 35-092 | 35-092-BU | 5 | On Off | SPST | | | 16 | | Paddle* | Green | 0.342 | 0.500 | QC .250″ | N, LN | 271-E |
| 35-094 | 35-094-BU | 5 | On Off | SPST | | | 16 | | Paddle* | Amber | 0.342 | 0.500 | QC .250″ | N, LN | 271-E |
| 35-3008 | 35-3008-BU | 6 | On Off | SPST | 15 | 10 | | 3/4 | Paddle | Black | | 0.550 x 1.125 | QC .250″ | N, LN | 271-F |
| 35-3091 | 35-3091-BU | 7 | On Off | SPST | 15 | 10 | | 3/4 | Paddle** | Amber | | 0.550 x 1.125 | QC .250″ | N, LN | 271-F |
| 35-3092 | 35-3092-BU | 7 | On Off | SPST | 15 | 10 | | 3/4 | Paddle** | Red | | 0.550 x 1.125 | QC .250″ | N, LN | 271-F |
| 35-3140 | 35-3140-BU | 8 | On Off | SPST | 15 | 10 | | 3/4 | Paddle* | Red/Green | 0.379 | 0.500 | QC .250″ | N, FN | 271-G |

Notes: *Lighted Paddles (12V Incandescent)
**Lighted Base (125 V Neon)
FN=Face Nut
HP=Horse Power
LN=Locking Nut
N=Nut
QC=Quick Connect

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.



Phone (815)316-9080•Fax (815)316-9081

All quantities are single; BU's are packages of 10 Unless otherwise noted.

## MINIATURE TOGGLES (Cont.)

**A**




**B**




**C**




**D**




## MEDIUM DUTY TOGGLES

**E**




**F**




**G**







All quantities are single; BU's are packages of 10 Unless otherwise noted.

## MEDIUM DUTY TOGGLES (Cont.)

Fig. 1

Fig. 2

Fig. 3

Fig. 4

Fig. 5

Fig. 6

Fig. 7

Fig. 8

Fig. 9

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/ Throws | Amps 125VAC | Amps 250VAC | HP 125-250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **35-132** | **35-132-BU** | 1 | On On | DPDT | 3 | | | Bat | Metal | 0.418 | 0.500 | Solder | 2 N, ID | 273-A |
| **35-064** | **35-064-BU** | 2 | On Off | SPST | 4 | 2 | | Bat | Metal | 0.418 | 0.500 | Solder | 2 N, ID | 273-A |
| **35-076** | **35-076-BU** | 3 | Off (On) | SPST | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-B |
| **35-086** | **35-086-BU** | 3 | On Off (On) | SPDT | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-B |
| **35-114** | **35-114-BU** | 3 | On On | SPDT | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-B |
| **35-116** | **35-116-BU** | 3 | On (On) | SPDT | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-B |
| **35-117** | **35-117-BU** | 4 | On On | DPDT | 6 | 3 | 1/4 | Bat | Metal | 0.468 | 0.500 | QC .250″ | N, KN | 273-C |
| **35-118** | **35-118-BU** | 4 | On Off | DPST | 6 | 3 | | Bat | Metal | 0.468 | 0.500 | QC .250″ | N, KN | 273-C |
| **35-154** | **35-154-BU** | 5 | On (On) | DPDT | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-D |
| **35-160** | **35-160-BU** | 6 | On Off | SPST | 6 | 3 | | Bat | Metal | 0.465 | 0.500 | Solder | N, KN | 273-E |
| **35-167** | **35-167-BU** | 7 | On Off | SPST | 6 | 3 | | Bat | Metal | 0.470 | 0.500 | Screw | N, KN, Sc | 273-F |
| **35-171** | **35-171-BU** | 8 | On Off | SPST | 6 | 3 | | Ball | Metal | 0.276 | 0.500 | Screw | N, KN, Sc, ID | 273-G |
| **35-186** | **35-186-BU** | 9 | On On | DPDT | 6 | 3 | 3/4 | Paddle | Black Plastic | 0.379 | 0.500 | Solder | N, KN | 273-H |
| **35-188** | **35-188-BU** | 9 | On Off On | DPDT | 6 | 3 | 3/4 | Paddle | Black Plastic | 0.379 | 0.500 | Solder | N, KN | 273-H |

Notes: (On)=Momentary On
*Rated 20A @ 125-277VAC
HP=Horse Power
ID=ID Plate
KN=Knurled Nut
NN=Nickel Nut
N=Nut(s)
QC=Quick Connect
WL=Wire Lead
Sc=Screw

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.





Phone (815)316-9080•Fax (815)316-9081

All quantities are single; BU's are packages of 10 Unless otherwise noted.

**A**




**B**




**C**




**D**




**E**




**F**




**G**




**H**








All quantities are single; BU's are packages of 10 Unless otherwise noted.

## MEDIUM DUTY TOGGLES (Cont.)

Fig. 1

Fig. 2

Fig. 3

Fig. 4

Fig. 5

Fig. 6

Fig. 7

Fig. 8

Fig. 9

Fig. 10

Fig. 11

| Retail Part No. | Bulk Part No. | Fig. No. | Circuit Function | Poles/ Throws | Amps 125VAC | Amps 250VAC | HP 125-250VAC | Actuator Style | Actuator Material | Bushing Length | Mounting Hole | Terminal Type | Hardware | Spec. Drawing Page No. |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| **35-854** | **35-854-BU** | 1 | On Off | SPST | 6 | 3 | | Bat | Black Plastic | 0.342 | 0.500 | WL | KN, ID | 275-A |
| **35-1076** | **35-1076-BU** | 2 | Off (On) | SPST | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Screw | N, KN, FN, Sc | 275-B |
| **35-1114** | **35-1114-BU** | 2 | On On | SPDT | 6 | 3 | 1/4 | Bat | Metal | 0.465 | 0.500 | Screw | N, KN, FN, Sc | 275-B |
| **35-1116** | **35-1116-BU** | 2 | On (On) | SPDT | 6 | 3 | 1/4 | Bat | Brass | 0.465 | 0.500 | Screw | N, KN, FN, Sc | 275-B |
| **35-3035** | **35-3035-BU** | 3 | On Off | SPST | 6 | 3 | | Bat | Brass | 0.325 | 0.500 | Screw | 2 N | 275-C |
| **35-119** | **35-119-BU** | 4 | On Off | SPST | 10 | 5 | 1/2 | Bat | Metal | 0.500 | 0.500 | QC .250″ | N, KN | 275-D |
| **35-120** | **35-120-BU** | 4 | On On | SPDT | 10 | 5 | 1/2 | Bat | Metal | 0.500 | 0.500 | QC .250″ | N, KN | 275-D |
| **35-180** | **35-180-BU** | 5 | On Off | SPST | 10 | 5 | 1/2 | Paddle | Black Plastic | 0.280 | 0.500 | QC .250″/Sd | FN, NN | 275-E |
| **35-182** | **35-182-BU** | 5 | On On | SPDT | 10 | 5 | 1/2 | Paddle | Black Plastic | 0.280 | 0.500 | QC .250″/Sd | FN, NN | 275-E |
| **35-184** | **35-184-BU** | 5 | On Off On | SPDT | 10 | 5 | 1/2 | Paddle | Black Plastic | 0.280 | 0.500 | QC .250″/Sd | FN, NN | 275-E |
| **35-3050** | **35-3050-BU** | 6 | On Off | SPST | 10 | 4 | 1/3 | Bat | Brass | 0.325 | 0.500 | WL | 2 N | 275-F |
| **35-112** | **35-112-BU** | 7 | On Off | DPST | 15 | 10 | | Bat | Metal | 0.468 | 0.500 | Solder | N, KN | 275-G |
| **35-152** | **35-152-BU** | 7 | On On | DPDT | 15 | 10 | | Bat | Metal | 0.468 | 0.500 | Solder | N, KN | 275-G |
| **35-3127** | **35-3127-BU** | 11 | (On) Off (On)† | DPDT | 15 | 10 | 1/2 | Bat | Metal | 0.465 | 0.500 | QC .250″ | FN, N | 275-H |
| **35-3153** | **35-3153-BU** | 8 | (On) Off (On) | SPDT | 15 | 10 | 3/4 | Paddle | Black Nylon | 0.379 | 0.500 | QC .250″ | FN, NN | 275-I |
| **35-3169** | **35-3169-BU** | 9 | (On) Off (On) | SPDT | 15 | 10 | 3/4 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |
| **35-178** | **35-178-BU** | 10 | On Off | SPST | 20 | 20 | ** | Paddle | Black Plastic | 0.342 | 0.500 | QC .250″/Sd | N, BFN | 275-K |
| **35-3009** | **35-3009-BU** | 5 | On Off | SPST | 20 | 10 | 1-1/2 | Paddle | Black Nylon | 0.280 | 0.500 | QC .250″/Sd | KN | 275-E |
| **35-3150** | **35-3150-BU** | 8 | On Off On | SPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | QC .250″ | FN, NN | 275-I |
| **35-3154** | **35-3154-BU** | 8 | On Off | DPST | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | QC .250″ | FN, NN | 275-I |
| **35-3156** | **35-3156-BU** | 8 | On On | DPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | QC .250″ | FN, NN | 275-I |
| **35-3158** | **35-3158-BU** | 8 | On Off On | DPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | QC .250″ | FN, NN | 275-I |
| **35-3160** | **35-3160-BU** | 9 | On Off | SPST | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |
| **35-3162** | **35-3162-BU** | 9 | On On | SPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |
| **35-3164** | **35-3164-BU** | 9 | On Off | DPST | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |
| **35-3166** | **35-3166-BU** | 9 | On On | DPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |
| **35-3168** | **35-3168-BU** | 9 | On Off On | DPDT | 20* | | 1-1/2 | Paddle | Black Nylon | 0.379 | 0.500 | Screw | FN, NN, Sc | 275-J |

Notes: (On)=Momentary On
*Rated 20A @ 125-277VAC
BFN=Brass Face Nut
FN=Face Nut
HP=Horse Power
ID=ID Plate
KN=Knurled Nut
NN=Nickel Nut
N=Nut(s)
QC=Quick Connect
Sc=Screw
Sd=Solder
WL=Wire Lead
†=Reversing Toggle
**=1/2 HP@125V, 1 HP@250V

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.





Phone (815)316-9080•Fax (815)316-9081

All quantities are single; BU's are packages of 10 Unless otherwise noted.

**A**




**B**




**C**




**D**




**E**




**F**




**G**




**H**




**I**




**J**




**K**