


Ferrules INSULATED (INDUSTRIAL STANDARD)

DIN Code <Polypropylene insulated and tin-plated electrolytic copper>




DIN 46228, part 4

Model No.	Applicable wire		Style	Colour Code	Dimensions (mm)				
	mm2	AWG			L1	L2	D1	S1	D2
DWE0.5-8	0.50	20	II	White	14	8	1	0.15	2.6
DWE0.75-8	0.75	18	II	Grey	14	8	1.2	0.15	2.8
DWE1-8	1.00	18	II	Red	14	8	1.4	0.15	3
DWE1.5-8	1.50	16	I	Black	14	8	1.7	0.15	3.5
DWE2.5-8	2.50	14	I	Blue	14	8	2.2	0.15	4.2
DWE4-10	4.00	12	I	Grey	17	10	2.8	0.2	4.8
DWE6-12	6.00	10	I	Yellow	20	12	3.5	0.2	6.3
DWE10-12	10.0	8	I	Red	22	12	4.5	0.2	7.6
DWE16-12	16.0	6	II	Blue	24	12	5.8	0.2	8.8
DWE25-16	25.0	4	I	Yellow	30	16	7.3	0.2	11.2
DWE35-16	35.0	2	I	Red	30	16	8.3	0.2	12.7
DWE50-20	50.0	1	I	Blue	36	20	10.3	0.3	15

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard
2) Maximum operating temperature: + 105°C
3) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates;
J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.

Twin Cable ferrules <Polypropylene insulated and tin-plated electrolytic copper>



DIN Colour Code

Model No.	Applicable Wire		Style	Colour Code	Dimensions					
	2 x mm2	2 x AWG			L1	L2	D1	S1	D2	E
TWE0.5-8	0.50	20	II	White	16	8	1.5	0.15	4.9	2.5
TWE0.75-8	0.75	18	II	Grey	16	8	1.8	0.15	5.2	2.6
TWE1-8	1.00	18	II	Red	16	8	2.3	0.15	5.8	3.2
TWE1.5-8	1.50	16	II	Black	16	8	2.3	0.15	6.5	3.6
TWE1.5-12	1.50	16	II	Black	20	12	2.3	0.15	6.5	3.6
TWE2.5-10	2.50	14	II	Blue	18	9	2.9	0.15	7.5	4.3
TWE4-12	4.00	12	II	Grey	23	12	3.8	0.20	9	5.2
TWE6-14	6.00	10	II	Yellow	26	14	4.9	0.20	10	7.2
TWE10-12	10.0	8	II	Red	24	12	5.8	0.20	14.5	7.5
TWE16-16	16.0	6	II	Blue	29	16	8.3	0.22	18.3	9.3

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard
2) Maximum operating temperature: + 105°C
3) Do not twist the strands
4) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates;
J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.