

BOX MOUNT D-SUB CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

PLUG ASSY,62 POSN,AMPLIMITE

AMPLIMITE | AMPLIMITE

206502-1

TE Internal Number: 206502-1

Mil-Spec: 311P407-4P-B-15

Alias ID: 0-0206502-1

EU RoHS Compliant

EU ELV Compliant

Connector Style Plug

Number of Positions 62

Power/Signal/Coax Combination No

Shell Size 4

Contact Style Crimp Snap-In

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

AMPLIMITE NONMAGNETIC PLUG ASSEMBLY, SERIES 90, SHELL SIZE 4, 62 POSITION

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Instruction Sheets

Instruction Sheet (U.S.)

AMPLIMITE NON-MAGNETIC HIGH DENISTY 22 (HD-22) CONNECTORS

PDF

English

AMPLIMITE NON-MAGNETIC HIGH DENISTY 22 (HD-22) CONNECTORS

TIF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Plug

Shell Size 4

Blindmate No

Product Type Connector

Configuration Features

Number of Positions 62

Power/Signal/Coax Combination No

Body Features

Non-Magnetic Yes

Shell Material Brass

Shell Plating Material Gold

Insert Arrangement MA18276-2

Retention Clip Material Copper Alloy

Contact Features

Contact Style Crimp Snap-In

Contact Size 22

Contact Type Pin

Mechanical Attachment

Mounting Hole Diameter 3.91 mm [.154 in]

Operation/Application

ULTRA-LITE Connector No

Packaging Features

Packaging Method Package

Statement of Compliance

Statement of Compliance

PDF
