



Specifications
Current Rating: 3amp
Insulation Resistance: 1000M Ω Min.
Dielectric Withstanding: 600V AC/DC
Contact Resistance: 20m Ω Max.
Operating Temperature:-40°C to +105°C

Materials

Contact Material: Copper Alloy
Insulation Material: Polyester, UL 94V-0 P.B.T
Contact plating: Gold Flash
All materials must be GP materials



NUMBER OF POSITIONS	Dimensions		
	A	B	C
10	32.00	21.84	10.16
14	37.08	26.92	15.24
16	39.62	29.46	17.78
20	44.70	34.54	22.86
26	52.32	42.16	30.48
30	57.40	47.24	35.56
34	62.48	52.32	40.64
40	70.10	59.94	48.26
50	82.80	72.64	60.96
60	95.50	85.34	73.66
64	100.58	90.42	78.74

CnC Tech, LLC

Industrial Cable and Connector Technology

DESIGN <i>Samayk</i>	PART NO.	3010-XX-002-11-00	
DATE 2011.12.05	REV A	SIZE A4	UNLESS OTHERWISE SPECIFIED TOLERANCES ANG $\pm 5^{\circ}$ 0 ± 0.3 .0 ± 0.15 .00 ± 0.10
CHECKED	UNIT mm		