



CABLE TYPE	
	RG 58C/U (Black)
Model No.	5266-C-XX
Cap. PF/Ft.	30.8
Nom. Imp.	50

### FEATURES:

- Is the same high quality construction as Model 2249-C with a connector on one end only.

### MATERIALS:

Connectors: BNC Male

Body: Brass, Tarnish resistant plating

Dielectric: PTFE

Center Contact – Gold Plated Brass

Strain Relief: PVC molded directly to cable and connectors

Marking: “Pomona 5266-C-XX”

### RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

### ORDERING INFORMATION: Model 5266-C-XX

XX = Cable Lengths, Standard Length: 60” (1524),

Additional lengths can be quoted upon request.

Ordering Example: 5266-C-60 Indicates 60” in length.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Sales: 909-469-2900 Fax: 909-629-3317  
Technical Assistance: 800-241-2060