





1.5 (PITCH)



10CKTのロック形状
FIGURE OF 10 CIRCUIT



8CKTのロック形状
FIGURE OF 8 CIRCUIT



24.0	29.8	503149340*	34
22.5	28.3	503149320*	32
21.0	26.8	503149300*	30
19.5	25.3	503149280*	28
18.0	23.8	503149260*	26
16.5	22.3	503149240*	24
15.0	20.8	503149220*	22
13.5	19.3	503149200*	20
12.0	17.8	503149180*	18
10.5	16.3	503149160*	16
9.0	14.8	503149140*	14
7.5	13.3	503149120*	12
6.0	11.8	503149100*	10
4.5	10.3	503149080*	8
B	A	MATERIAL AND ORDER No.	CIRCUIT No.

REVISED EC NO: J2015-0528 DRWN: TAKAIKE CHKD: ASAKAWA APPR: NUKITA	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		0.25 UNDER		± 0.03	DRAWN BY T. HANYU	DATE 2008/1/8	TITLE 1.5 W/B CONN. DUAL PLUG HOUSING			
		0.25 OVER 0.5 UNDER		± 0.05	CHECKED BY K. ASAKAWA	DATE 2008/1/8				
		0.5 OVER 1.0 UNDER		± 0.1	APPROVED BY YO. ITO	DATE 2008/1/8	molex			
		1.0 OVER 10 UNDER		± 0.2	MATERIAL NO.			DOCUMENT NO. SD-503149-001		
		10 OVER 30 UNDER		± 0.25	SEE TABLE					SHEET NO. 1 OF 2
		30 OVER		± 0.3						
		ANGULAR ±1 °								
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

NOTES

1. 材料 PBT UL94V-0
MATERIAL
- ④ 2. 嵌合相手 : 503148, 503154, 505406 シリーズ
MATE WITH : 503148, 503154, 505406 SERIES
3. 適合ターミナル : 502579, 503429 シリーズ
APPLICABLE TERMINAL : 502579, 503429 SERIES
- △ 4. 極数 / 2 = 偶数極の場合に適用
APPLY FOR (CIRCUIT/2=EVEN)
- △ 5. 製品番号
MATERIAL No.

503149 - **0*

極数

CIRCUIT SIZE

色

COLOR

COLOR	黒 BLACK	赤 RED	青 BLUE	緑 GREEN	ベージュ BEIGE (NATURAL)
COLOR No.	1	2	4	6	0

6. 本製品のプラスチック部に黒点・白点等が確認される場合や
色合いが異なる場合がありますが、製品性能に問題はありません。
THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH
THE BLACK AND WHITE SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC
PART OF THIS PRODUCT AND THE SADE MIGHT BE DIFFERENT.
- △ 7. トレードマーク : M プラス 2 文字の製造工場を示すアルファベットにて表示。
'但し, "J" は JAPAN を "L" は MALAYSIA を示す。(例 MXJ 又は MXL) '
金型番号 : アルファベット 1 文字にて表示。(例 1A, 12A, 1B, 12B)
FORMED BY M AND FROM 1 TO 2 MORE LETTER OF ALPHABET
WHICH MEAN THE MANUFACTORY.
'BUT "J" MEANS JAPAN. "L" MEANS MALAYSIA (TO TRADE MARK)'
(e.g. MXJ OR MXL)
AND BY 1 - 2 DIGIT NUMBER (TO CAVITY NO.)
"AND BY 1 LETTER OF ALPHABET (TO MOLD NO.)"(e.g. 1A, 12A, 1B, 12B)."
8. アプリケーション仕様書 (コネクタ取扱説明書) : AS-503149-001
APPLICATION SPECIFICATIONS (CONNECTOR MANUAL) : AS-503149-001
9. 製品仕様書 : PS-503148-001 / PS-503154-001
PRODUCT SPECIFICATION : PS-503148-001 / PS-503154-001
10. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT
- △ 11. 34 極品の色対応はベージュと黒色のみとなります。
A COLOR OF 34CKT. IS ONLY BEIGE AND BLACK.

REVISED

EC No. J2015-0528

DRWN: TAKAIKE

CHKD: KASAKAWA

APPR: NUKITA

H

DESCRIPTION

2014/10/23

2015/02/16

2015/02/16

REV

GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
0.25 UNDER	± 0.03	DRAWN BY	DATE	TITLE 1.5 W/B CONN. DUAL PLUG HOUSING			
0.25 OVER 0.5 UNDER	± 0.05	T. HANYU	2008/1/8				
0.5 OVER 1.0 UNDER	± 0.1	CHECKED BY	DATE	1.5 W/B CONN. DUAL PLUG HOUSING			
1.0 OVER 10 UNDER	± 0.2	K. ASAKAWA	2008/1/8				
10 OVER 30 UNDER	± 0.25	APPROVED BY	DATE	molex			
30 OVER	± 0.3	Y0. ITO	2008/1/8				
ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 1		SD-503149-001		2 OF 2	
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					