



RED INDICATES ORIGINAL

DWG
SIZE
C

DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS, INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR REPRODUCTION OR ANALYSIS WITHOUT
EXPRESS WRITTEN PERMISSION.

REVISIONS			12-01	SH 1
REV	CD	DESCRIPTION	DWN	DATE
J	11191	ADDED C.J70TL, -201 THRU -220; ADDED ITEM 34; SEE ECD	DKC	

P2 CONN TYPE	FIG NO	P1 CONN TYPE																			
		BJ20					UBJ20					BJ40					UBJ40				
		SCHEMATICS																			
		E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5
		DASH NUMBERS																			
BJ74	1A	-1	-2	-3	-4	-169	-5	-6	-7	-8	-9	-10	-11	-12	-171	-13	-14	-15	-16	-17	
BJ74TL	1A	-17	-18	-19	-20	-173	-21	-22	-23	-24	-174	-25	-26	-27	-28	-175	-29	-30	-31	-32	-176
BJ74FL	1A	-33	-34	-35	-36	-177	-37	-38	-39	-40	-178	-41	-42	-43	-44	-179	-45	-46	-47	-48	-180
BJ374	1B	-49	-50	-51	-52	-181	-53	-54	-55	-56	-182	-57	-58	-59	-60	-183	-61	-62	-63	-64	-184
BJ79	2A	-65	-66	-67	-68	-185	-69	-70	-71	-72	-186	-73	-74	-75	-76	-187	-77	-78	-79	-80	-188
BJ79TL	2A	-81	-82	-83	-84	-189	-85	-86	-87	-88	-190	-89	-90	-91	-92	-191	-93	-94	-95	-96	-192
BJ79FL	2A	-97	-98	-99	-100	-193	-101	-102	-103	-104	-194	-105	-106	-107	-108	-109	-110	-111	-112	-113	-195
BJ379	2B	-113	-114	-115	-116	-197	-117	-118	-119	-120	-198	-121	-122	-123	-124	-125	-126	-127	-128	-129	-200
CJ70	3A	-129	-130	-131	-132	-133	-134	-135	-136	-137	-138	-139	-140	-141	-142	-143	-144	-145	-146	-147	-148
CJ370	3B	-149	-150	-151	-152	-153	-154	-155	-156	-157	-158	-159	-160	-161	-162	-163	-164	-165	-166	-167	-168
CJ70TL	3A	-201	-202	-203	-204	-205	-206	-207	-208	-209	-210	-211	-212	-213	-214	-215	-216	-217	-218	-219	-220




INCH	MM
.005	0.13
.030	0.76
.109	2.77
.140	3.56
.218	5.54
.221	5.61
.281	7.14
.284	7.21
.505	12.83
.510	12.95
.593	15.06
.625	15.88
.630	16.00
.635	16.13
.687	17.45
.750	19.05
.800	20.32
1.835	46.61

△ FOR OPTIONAL GROUND
TERMINAL ADD PREFIX "G"
TO DASH NO (-G1 ETC)

3. BETWEEN SERIES ADAPTER,
50 & 75 OHM
BNC/TNC COAXIAL JACK TO
CONCENTRIC TWINAX/TRIAX INSULATED &
NONINSULATED BULKHEAD MOUNT JACK

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES



RECOMMENDED
PANEL CUTOUT
FOR -1 THRU -64
MAX PNL THK .140



FIG 1A (P1)
-1 SHOWN
-57 SHOWN
FIG 1B (P1)







FIG 2A (P1)
-65 SHOWN
-121 SHOWN
FIG 2B (P1)



RECOMMENDED
PANEL CUTOUT
FOR -65 THRU -128
MAX PNL THK .109

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED			
.100 ±			
.005 ±			
.0000 ±			
ANGLE ±			
DWN	DKC	8-1-85	
CHK			
ENGR			
APPR			
TROMPETER ELECTRONICS, INC.		ADAPTERS: U/BJ20/40 TO "70" SERIES BULKHEAD MOUNT	
MATERIAL		CODE IDENT	DRAWING NO.
14949		14949	12-01
SCALE 2/1		DATE 8/17/85	SHEET 1 OF 2
NEXT ASSY			REV J