

DeviceNet™, minifast® Field Wireable Connectors

- Allows for Quick Connection when Pre-Molded Cables not Available
- Available for Male and Female Connectors
- Color Coded Wire Connections for DeviceNet



Housing	Part Number	Housing Specs.	Application	Pinouts
	BS 4151-0/9/DNET	Glass filled nylon PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals 85°C 250 V, 9 A	Mates with all 5-pin cordsets and receptacles	Male
	BS 4151-0/13.5/DNET	Glass filled nylon PG 13.5 cable gland accepts 10-12 mm cable diameter Screw terminals 85°C 250 V, 9 A		
	B 4151-0/9/DNET	Glass filled nylon PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals 85°C 250 V, 9 A		Female
	B 4151-0/13.5/DNET	Glass filled nylon PG 13.5 cable gland accepts 10-12 mm cable diameter Screw terminals 85°C 250 V, 9 A		