



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'PESS-B-N'

Your search criteria matched only one product, shown below

PESS-B-N



- Resistant to temperatures up to 275°F (135°C)

	Part Number	PESSB-N
	RoHS Compliancy Status	Compliant
	Part Description	Conductor ID Label, 16mm Dia, 'N'
	Material	GMY Polyester
	Color (Legend/Background)	White/Blue
	Legend	NEUTRAL CONDUCTOR N
	Marker Diameter (In.)	.63
	Marker Diameter (mm)	16.00
	Markers Per Card	20
	Meaning	Alternating Current Neutral Conductor
	Pricing Description	Card Label, Polyester, 'N', 0.63" dia., 20/card, 10 cards/pk, WH/BL
	Style	B
	Min. Order UOM	CG
	Min. Order Qty.	10
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.