

MINIATURE LAMP (927) Details

Part #	927				
Description	T5 WEDGE 6.0V 1.2A 8.0CP				
Bulb Shape	T-5	Filament	C-2R	Base Style	Wedge (T-5)
Glass Diameter (in)	0.63	MOL [†] (in)	1.49	LCL ^{††} (in)	0.81
Glass Diameter (mm)	16	MOL (mm)	37.80	LCL (mm)	20.60
Volts	6	MSCP [‡]	8	Avg Life Hrs	50
Watts	7.2	Amps	1.20	RoHS Compliant	Yes
E-Marked	No				



[†] MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

[‡] MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

^{††} LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.