




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	TRANSFER ECOC	07/03	—	CA
	B1	REVISED PER ECO-18-002105	27FEB2018	RS	DR

AMP
WIRE RANGE

12-10 AWG
SOLID OR STRANDED

- 1
- STAMP AMP 12-10* APPROX AS SHOWN

2

MATERIAL: COPPER PER ASTM B152,ANNEALED

3

FINISH: NICKEL PLATE 0.00762[.000300] MIN
EXT THK PER SAE AMS QQ-N-290

PRELIMINARY	5000	BULK/BAG	132005-2
	500	LOOSE PIECE	132005-1
	QUANTITY	PACKAGING TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27FEB2018 RAVI S		TE Connectivity Ltd.	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX. RECOMMENDED OPERATING TEMPERATURE: 343°C [649°F] MAX	DIMENSIONS: mm [INCHES]	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°	CHK 27FEB2018 ROHDE DANIEL F	APVD 27FEB2018 ROHDE DANIEL F	NAME	TERMINAL,STRATO-THERM,HR,FLAG 12-10 AWG —
FOR APPLICATION	TOOLING ASSISTANCE CENTER	VOLTAGE RATING: NOT APPLICABLE	MATERIAL	FINISH	APPLICATION SPEC	WEIGHT	SIZE A2	CAGE CODE 00779
TOOLING INFORMATION	1-800-722-1111							
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 2.62-6.64mm²[5,180-13,100] CIR MILS SOLID OR STRANDED	CUSTOMER DRAWING	SCALE 8:1	SHEET 1 of 1	REV B1	DRAWING NO C-132005	RESTRICTED TO —