


LDA Series Single Output — 10-300 Watts Universal Input AC 85~264, Open Frame

Designed for Small Size, Low Profile, High Reliability and Low Cost.



- Cost Effective, Small, Open Frame PC Board Construction

► High Quality — Field Failure Rate Less than 0.012%

► Available with Chassis and Cover (SN Option)

► Available with Chassis, Cover and Fan Option (SNF Option), LDA300W

► Also Available with ±10% Adjustable Output Potentiometer (Y Option)

► Universal Input LDA 10-75 Watts (AC 85~264), LDA 100, 150, 300 Watts (AC 85~132, 170~264)
- Fully Regulated, Fully Isolated Input/Output

► Inrush Current, Over-Voltage Protection Circuitry

► Remote Sensing LDA200

► Conductive Noise — Complies with FCC-B, VCCI-2 and VGF 243/91

► UL, CSA and TUV Safety Approvals; CE Marked

► Two Year Warranty

► Wiring Harnesses Available at Bottom of Page 696

Stock No.	Mfr.'s Type	DC Output Voltage						Size (In.) W × H × D	Weight (Lbs.)	EACH	
		3	5	12	15	24	48			1-4	5-24
800-5600	LDA10F-3	2.0 A	—	—	—	—	—	1.96 × 0.82 × 4.13	0.17	32.59	30.08
800-5605	LDA10F-3-SN	2.0 A	—	—	—	—	—	2.25 × 1.29 × 4.92	0.17	36.07	33.30
800-9200	LDA10F-5	—	2.0 A	—	—	—	—	1.96 × 0.82 × 4.13	0.17	35.00	32.00
800-9300	LDA10F-5-SN	—	2.0 A	—	—	—	—	2.25 × 1.26 × 4.92	0.17	36.07	33.30
800-9205	LDA10F-12	—	—	0.9 A	—	—	—	1.96 × 0.82 × 4.13	0.17	35.00	32.00
800-9305	LDA10F-12-SN	—	—	0.9 A	—	—	—	2.25 × 1.26 × 4.92	0.17	36.07	33.30
800-9210	LDA10F-15	—	—	—	0.7 A	—	—	1.96 × 0.82 × 4.13	0.17	32.59	30.08
800-9215	LDA10F-24	—	—	—	—	0.5 A	—	1.96 × 0.82 × 4.13	0.17	35.00	32.00
800-9315	LDA10F-24-SN	—	—	—	—	0.5 A	—	2.25 × 1.26 × 4.92	0.17	36.07	33.30
800-5610	LDA15F-3	3.0 A	—	—	—	—	—	1.96 × 0.82 × 4.92	0.21	43.28	39.95
800-5615	LDA15F-3-SN	3.0 A	—	—	—	—	—	2.25 × 1.26 × 5.71	0.21	47.01	43.40
800-9220	LDA15F-5	—	3.0 A	—	—	—	—	1.96 × 0.82 × 4.92	0.21	43.28	39.54
800-9225	LDA15F-12	—	—	1.3 A	—	—	—	1.96 × 0.82 × 4.92	0.21	43.28	39.95
800-9325	LDA15F-12-SN	—	—	1.3 A	—	—	—	2.25 × 1.26 × 5.71	0.21	47.01	43.40
800-9335	LDA15F-24-SN	—	—	—	—	0.7 A	—	2.25 × 1.26 × 5.71	0.21	47.01	43.40
800-5620	LDA30F-3	6.0 A	—	—	—	—	—	2.17 × 1.02 × 5.24	0.44	55.97	51.66
800-5625	LDA30F-3-SN	6.0 A	—	—	—	—	—	2.56 × 1.42 × 6.42	0.44	60.70	56.03
800-9240	LDA30F-5	—	6.0 A	—	—	—	—	2.17 × 1.02 × 5.24	0.44	55.97	51.66
800-9340	LDA30F-5-SN	—	6.0 A	—	—	—	—	2.56 × 1.42 × 6.42	0.44	60.70	56.03
800-9245	LDA30F-12	—	—	2.5 A	—	—	—	2.17 × 1.02 × 5.24	0.44	55.97	51.66
800-9345	LDA30F-12-SN	—	—	2.5 A	—	—	—	2.56 × 1.42 × 6.42	0.44	60.70	56.03
800-9250	LDA30F-15	—	—	—	2.0 A	—	—	2.17 × 1.02 × 5.24	0.44	55.97	51.66
800-9255	LDA30F-24	—	—	—	—	1.3 A	—	2.17 × 1.02 × 5.24	0.44	55.97	51.66
800-9355	LDA30F-24-SN	—	—	—	—	1.3 A	—	2.56 × 1.42 × 6.42	0.44	64.00	59.00
800-5630	LDA50F-3	10.0 A	—	—	—	—	—	2.17 × 1.02 × 7.68	0.55	70.90	65.44
800-5635	LDA50F-3-SN	10.0 A	—	—	—	—	—	2.56 × 1.42 × 8.86	0.55	76.37	70.49
800-9360	LDA50F-5-SN	—	10.0 A	—	—	—	—	2.56 × 1.42 × 8.86	0.55	76.37	70.49
800-9265	LDA50F-12	—	—	4.3 A	—	—	—	2.17 × 1.02 × 7.68	0.55	70.90	65.44
800-9365	LDA50F-12-SN	—	—	4.3 A	—	—	—	2.56 × 1.42 × 8.86	0.55	76.37	70.49
800-9270	LDA50F-15	—	—	—	3.5 A	—	—	2.17 × 1.02 × 7.68	0.55	70.90	65.44
800-9275	LDA50F-24	—	—	—	—	2.1 A	—	2.17 × 1.02 × 7.68	0.55	70.90	65.45
800-9375	LDA50F-24-SN	—	—	—	—	2.1 A	—	2.56 × 1.42 × 8.86	0.55	76.37	70.49
800-5640	LDA75F-3	15.0 A	—	—	—	—	—	2.17 × 1.26 × 8.74	0.70	89.05	82.20
800-5645	LDA75F-3-SN	15.0 A	—	—	—	—	—	2.56 × 1.65 × 9.93	0.70	96.02	88.63
800-0025	LDA75F-5	—	15.0 A	—	—	—	—	2.17 × 1.26 × 8.74	0.70	89.05	82.20
800-4200	LDA75F-5-SN	—	15.0 A	—	—	—	—	2.56 × 1.65 × 9.93	0.70	96.02	88.63
800-0003	LDA75F-12	—	—	6.3 A	—	—	—	2.17 × 1.26 × 8.74	0.70	89.05	82.20
800-4205	LDA75F-12-SN	—	—	6.3 A	—	—	—	2.56 × 1.65 × 9.93	0.70	96.02	88.63
800-0035	LDA75F-15	—	—	—	5.0 A	—	—	2.17 × 1.26 × 8.74	0.70	89.05	82.20
800-4210	LDA75F-15-SN	—	—	—	5.0 A	—	—	2.56 × 1.65 × 9.93	0.70	96.05	88.63
800-0040	LDA75F-24	—	—	—	—	3.2 A	—	2.17 × 1.26 × 8.74	0.70	89.05	82.20
800-4215	LDA75F-24-SN	—	—	—	—	3.2 A	—	2.56 × 1.65 × 9.93	0.70	96.02	88.63
800-5650	LDA100W-3	20.0 A	—	—	—	—	—	2.44 × 1.38 × 8.74	0.79	115.42	106.54
800-5655	LDA100W-3-SN	20.0 A	—	—	—	—	—	2.84 × 1.77 × 9.93	0.79	122.89	113.43
800-0100	LDA100W-5	—	20.0 A	—	—	—	—	2.44 × 1.38 × 8.74	0.79	115.42	106.54
800-4220	LDA100W-5-SN	—	20.0 A	—	—	—	—	2.84 × 1.77 × 9.93	0.79	122.89	113.43
800-0110	LDA100W-12	—	—	8.5 A	—	—	—	2.44 × 1.38 × 8.74	0.79	115.42	106.54
800-4230	LDA100W-12-SN	—	—	8.5 A	—	—	—	2.84 × 1.77 × 9.93	0.79	122.89	113.43
800-0130	LDA100W-24	—	—	—	—	4.3 A	—	2.44 × 1.38 × 8.74	0.79	115.42	106.54
800-4240	LDA100W-24-SN	—	—	—	—	4.3 A	—	2.84 × 1.77 × 9.93	0.79	122.89	113.43
800-6500	LDA100W-48	—	—	—	—	—	2.0 A	2.44 × 1.38 × 8.74	0.79	115.42	106.54
800-5660	LDA150W-3	30.0 A	—	—	—	—	—	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-5665	LDA150W-3-SN	30.0 A	—	—	—	—	—	3.35 × 1.85 × 9.93	1.12	158.21	146.04
800-0140	LDA150W-5	—	30.0 A	—	—	—	—	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-0150	LDA150W-12	—	—	12.5 A	—	—	—	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-4250	LDA150W-12-SN	—	—	12.5 A	—	—	—	3.35 × 1.85 × 9.93	1.12	158.21	146.04
800-0160	LDA150W-15	—	—	—	10.0 A	—	—	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-4255	LDA150W-15-SN	—	—	—	10.0 A	—	—	3.35 × 1.85 × 9.93	1.12	158.21	146.04
800-0170	LDA150W-24	—	—	—	—	6.3 A	—	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-4260	LDA150W-24-SN	—	—	—	—	6.3 A	—	3.35 × 1.85 × 9.93	1.12	158.21	146.04
800-6505	LDA150W-48	—	—	—	—	—	3.0 A	2.95 × 1.46 × 8.74	1.12	150.75	139.15
800-5670	LDA300W-3	60.0 A*	—	—	—	—	—	4.40 × 1.91 × 10.41	2.50	226.96	209.72
800-2830	LDA300W-5-SNF	—	60.0 A	—	—	—	—	4.62 × 3.38 × 12.32	2.50	301.39	278.49
800-0235	LDA300W-12	—	—	27.0 A*	—	—	—	4.40 × 1.91 × 10.41	2.50	226.96	209.72
800-2835	LDA300W-12-SNF	—	—	27.0 A	—	—	—	4.62 × 3.38 × 12.32	2.50	301.39	278.49
800-0240	LDA300W-15	—	—	—	22.0 A*	—	—	4.40 × 1.91 × 10.41	2.50	226.96	209.72
800-0245	LDA300W-24	—	—	—	—	14.0 A*	—	4.40 × 1.91 × 10.41	2.50	226.96	209.72
800-2840	LDA300W-24-SNF	—	—	—	—	14.0 A	—	4.62 × 3.38 × 12.32	2.50	301.39	278.49
800-6510	LDA300W-48	—	—	—	—	—	6.3 A*	4.40 × 1.91 × 10.41	2.50	226.96	209.72

*Forced air required.