






FE077A Series

Axial

Ø 773mm (30")

- Shallow, rugged AC fans with a 3-phase external rotor motor. Blades permanently attached to the motor for optimum motor cooling and reliable long life operation.
- 7-sickle bladed profiled die-cast aluminium impeller.
- Mounting using 19 mm holes. Ready to install.
- Wiring via Delta or Y yields two different speed options.
- Electrical connection via terminal box.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
FE077-A/125850	2	9100	460Y	50/60	960	79	60	Ball	Leads	71.0
FE077-A/125850	1	11500	460 Delta	50/60	1450	85	60	Ball	Leads	71.0



ebmpapst

e-mail: sales@us.ebmpapst.com • TEL: 860-674-1515 • FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2004 © ebm-papst Inc. reserves the right to change any specifications or data without notice