

INTRODUCTION:

Adam Tech's Flat Cable DIP & Transition plugs are a one piece connector system that quickly and easily mass terminates flat cable then mounts directly to the PCB or PCB socket. These connectors are ideal for interconnecting PCB's in a permanent flat cable transition or satisfying disconnect applications. Our low profile design allows an increased board to board stacking density.

FEATURES:

Available in 8 – 64 positions
Eliminates need for two piece header & Socket set
Fast easy mass termination without stripping cable
Heavy duty Tin plated contacts
Low Profile, high density board to board stacking
Plugs into IC Socket or solders directly to PCB

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL94V-0
Optional Hi-Temp insulator: Nylon 6T, rated UL94V-0
Insulator Color: Black (Gray optional)
Contacts: Brass

Contact Plating:

G = Gold flash (30u" optional) over nickel underplate on contact area,
Tin over copper underplate on IDC area.
T = Tin over copper underplate overall

Electrical:

Operating voltage: 250V AC max.
Current rating: 3 Amp max
Contact resistance: 20 mΩ max. initial
Insulation resistance: 5000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Recommended cable size: 28 Awg stranded

Temperature Rating:


Operating temperature: -40°C to +105°C

PACKAGING:


Anti-ESD plastic trays

SAFETY AGENCY APPROVALS:

UL Recognized & CSA Certified, File no. E224053



ORDERING INFORMATION




OPTIONS:


Add designator(s) to end of part number
30 = 30 μin gold plating in contact area
GY = Gray color insulator
RT = Board retention

FTR SERIES



.100" X .100" (8P-64P)



A = .100 [2.54] x No. of Positions per row +.310 [7.88]
B = .100 [2.54] x No. of Spaces per row







FTR-14-T




Recommended PCB Layout

FDP SERIES

.100" X .300" (8P-20P)







FDP-14-T




Recommended PCB Layout

FDP SERIES

.100" X .600" (24P-40P)



FDP-24-T



Recommended PCB Layout

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADAM TECH:

[FTR-26-T](#) [FDP-40-T](#) [FDP-36-T](#) [FTR-16-T](#) [FTR-10-T](#) [FTR-34-T](#) [FDP-10-T](#) [FTR-50-T](#) [FDP-20-T](#) [FDP-24-T](#) [FTR-40-T](#) [FDP-08-T](#) [FTR-20-T](#) [FDP-16-T](#) [FTR-08-T](#) [FDP-28-T](#) [FDP-14-T](#)