


PART NO.	REV
1280 -101 -103	
PROPRIETARY NOTICE This drawing, and the designs and information contained thereon, are the property of Herman H. Smith, Inc. They are not to be reproduced or disclosed to third parties.	

ELECTRICAL RATING:
 Rated voltage - 125 VOLTS
 Current rating - 15 AMPS




LEAD WIRES:
 AWG #14 (plastic wire leads) & AWG #16 (ground lead), AWM, 600V, 105°C, 6" long with 1/2" strip length or per customer specs.

HARDWARE:
 Spring clip - spring steel, blue tempered

MOLDED MATERIAL:
 Black phenolic or white urea.
 Other colors available on special order.



CSA FILE NO. LR 9105 UL FILE NO. E18487



MOUNTING PANEL CUT-OUT
 RECOMMENDED PANEL THICKNESS
 1/32 TO 1/16

FIGURE 2

UNLESS OTHERWISE SPECIFIED

Threads are Unified National
 Series (UNL):
 External _____ Class 2A
 Internal _____ Class 2B
 Threads shall be to gauge fit after
 plating or other finish

Surfaces shall be smooth, and free
 of tool marks. Break all sharp
 corners, and remove burrs.

TOLERANCES

ALL DIMENSIONS IN: **INCHES**
 (MM)

Fractions _____ ± 1/64 (0,4)
 Decimals (.XX) _____ ± .010 (0,2)
 Decimals (.XXX) _____ ± .005 (0,1)
 Angles _____ ± 1°
 Hole Dia _____ + .003 (0,08)
 _____ - .001 (0,02)
 Concentricity to center axis _____ .002 (0,05)

HHSmith

TITLE

CONVENIENCE OUTLET

SCALE

STOCK

BY

CHK


APP

DATE

MATERIAL

FINISH

THIRD ANGLE PROJECTION



PART NO.

REV.

1280

ASSEM WITH				NEXT ASSY		LTR	DATE	CHANGE
REVISIONS								