

NAVIGATE THE CATALOG BY SECTION


[1](#)
[2](#)
[3](#)
[4](#)
[5](#)
[6](#)
[7](#)
[8](#)
[9](#)
[10](#)
[11](#)
[12](#)
[13](#)
[14](#)
[15](#)
[16](#)
[17](#)
[18](#)
[19](#)


LAPP ONLINE CATALOG

EPIC® Pin & Sleeve Connectors

20 Amp: North American Version

MULTIMAX Male Plugs



TECHNICAL DATA

Impact Resistance:

8J

Ambient Temperature:

-25°C to 70°C

Flame Resistance:

➤ **Glow Wire Test: Enclosure:**

850°C

➤ **Glow Wire Test: Contact Enclosure:**

850°C

➤ **Self-Extinguishing: Enclosure:**

UL94-V2

PART NUMBERS

Part Number	Voltage	# of Wires	# of Poles	Ground-Clock Position
700124FX	125	3	1+N+PE	4
700126FX	250	3	2+PE	6
700127FX	480	3	2+PE	7
700123FX	250 DC	3	2+PE	3
701132FX	125 / 250	4	2+N+PE	12
700139FX	3Ø250	4	3+PE	9
700137FX	3Ø480	4	3+PE	7
700135FX	3Ø600	4	3+PE	5
700149FX	3ØY 120 / 208	5	3+N+PE	9
700147FX	3ØY 277 / 480	5	3+N+PE	7
700145FX	3ØY 347 / 600	5	3+N+PE	5
700142FX	50-250 (500 Hz)	5	3+N+PE	2

MATING COMPONENTS

- [MULTIMAX Female Connector with Cable Sleeve, IP 44](#)
- [CEE Straight Female Panel Mount Receptacle, IP 44](#)
- [CEE 75° Female Internal Surface Mount Receptacle, IP 44](#)



DOWNLOAD PDF CATALOG PAGE

LAPP USA • LAPP CANADA • LAPP MEXICO

Headquarters: 29 Hanover Road, Florham Park, NJ 07932
800-774-3539 • FAX: 973-660-9330 • sales@lappusa.com