



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ PKI 10 A

PKI 10 A

datasheet for PKI 10 A
article number: 930103102



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 103-102
description:	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm.
typ:	PKI 10 A blau/blue
system:	4 mm system
order number:	930 103-102
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	4 mm socket (unsprung), 2 mm cross hole
type of termination:	M4 thread
rated voltage:	30 VAC / 60 VDC
rated current:	35 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-25 °C to +100 °C
drawing	
	