


Collar Nut



Material  
Heat treated to tensile strength class 10. Turned and milled.  
DIN 6331

489279

| T-Bolt Size<br>(mm) | S<br>(mm) | E<br>(mm) | M<br>(mm) | A<br>(mm) | D1<br>(mm) | Order Code | Price Each |
|---------------------|-----------|-----------|-----------|-----------|------------|------------|------------|
| M8                  | 13        | 15        | 12        | 3.5       | 18         | 137-8383   |            |
| M10                 | 16        | 18.4      | 15        | 4.0       | 22         | 137-8382   |            |
| M12                 | 18        | 20.7      | 18        | 4         | 25         | 137-8381   |            |
| M14                 | 21        | 24.2      | 21        | 4.5       | 28         | 137-8380   |            |
| M16                 | 24        | 27.7      | 24        | 5         | 31         | 137-8379   |            |
| M20                 | 30        | 34.6      | 30        | 6         | 37         | 137-8378   |            |
| M24                 | 36        | 41.5      | 36        | 6         | 45         | 137-8377   |            |