







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00		P2	REVISED PER ECO-11-004587	11MAR11	RK
						HMR



- 1

REELED FOR MINI APPLICATOR
- 2

.000030 GOLD OVER .000050 NICKEL
- 3

GOLD FLASH OVER NICKEL,.000030 GOLD ON CONTACT AREA
- 4

PREPLATED:(HALT).000078-.000158 BRIGHT TIN
- 5

.000050 GOLD OVER .000050 NICKEL
- 6

GOLD FLASH OVER NICKEL,.000015 GOLD ON CONTACT AREA
- 7

GOLD PLATING NOT REQUIRED IN THIS AREA
- 8

.000050 GOLD ON CONTACT AREA,GOLD FLASH AREA L OVER.000050/.000100 NICKEL ENTIRE CONTACT
- 9

SHEARED EDGES MAY BE UNPLATED
- 10

REELED FOR STANDARD APPLICATOR
- 11

CUT OUTS ON BOX AT MANUFACTURER'S OPTION
- 12

OBSOLETED PART NUMBER
- 13

PT.OF MEAS.FOR PLATING THICKNESS(INSIDE BEAMS)
- 14

.000015 GOLD IN THE CONTACT AREA, .000050 NICKEL OVER THE ENTIRE TERMINAL
- 15

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		12-7	914	1-87666-9
915 OBSOLETE	1-12-7	87667-6	87	1-87666-6
	1-12-1	87667-5	67	87666-5
	1-12-0	87667-4	57	87666-4
	12-9	87667-3	4	87666-3
	12-8	87667-2	37	87666-2
	12-7	87667-1	27	87666-1
PART NO.		LOOSE PIECE PART NO.	FINISH	1 PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	8/03/98	TE Connectivity			
		CHK	-				
DIMENSIONS: INCHES		APVD	-	NAME			
		PRODUCT SPEC	-				
		APPLICATION SPEC	-	CONTACT, FEMALE MOD IV, CRIMP SNAP-IN			
		WEIGHT	-				
MATERIAL		FINISH	SEE TABLE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
BERYLLIUM COPPER .008 THK. COMPL.				A2	00779	C=87666	-
CUSTOMER DRAWING				SCALE	8:1	SHEET	1 of 1
						REV	P2