




9 8 7 6 5 4 3 2 1

引き出し方向

PULL OUT
DIRECTION



"E"




DETAIL "E"

NOTES


- 梱包数量： 3000個 / リール
NUMBER OF CONNECTORS : 3000 PCS/REEL.
- リードテープ長さ
LEAD TAPE LENGTH

引き出し方向

PULL OUT
DIRECTION




- カバートープの剥離強度については、IEC60286-3に準拠。
COVER TAPE PEEL FORCE IS DEFINED BY IEC 60286-3.
- 製品詳細寸法については、図面 5051101001-000を参照下さい。
FOR DIMINTIONS OF PRODUCT, REFER TO 5051101001-000.
- 材料 MATERIAL
キャリアテープ : ポリスチレン
CARRIER TAPE : POLYSTYRENE
トップテープ : ポリエチレンテレフタレート、ポリエチレン
TOP TAPE : POLYETHYLENE TEREHTHALATE, POLYETHYLENE
リール :ポリスチレン<リサイクル材を含む>
REEL : POLYSTYRENE <RECYCLE MATERIAL CONTAINED >
- ELV及びRoHS適合品 ELV AND RoHS COMPLIANT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																								
EC DESCRIPTION EC NO: 100528 DRWN: NKONDO CHK'D: KTAKAHASHI APPR: KMORIKAWA		2015/06/30 2015/06/30 2015/06/30		QUALITY SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▼ = 0 ▽ = 0 ☒ = 0 ■ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0 ° <table><tr><td>4 PLACES</td><td>± 0.05</td></tr><tr><td>3 PLACES</td><td>± 0.1</td></tr><tr><td>2 PLACES</td><td>± 0.2</td></tr><tr><td>1 PLACE</td><td>± 0.2</td></tr><tr><td colspan="2">0 PLACES ± 0.2</td></tr></table>		4 PLACES	± 0.05	3 PLACES	± 0.1	2 PLACES	± 0.2	1 PLACE	± 0.2	0 PLACES ± 0.2		DIMENSION UNITS MM		SCALE 2:1		molex 0.5 FPC CONN ZIF E/O 2 CONT TYPE EMB PKG			
							4 PLACES	± 0.05																
							3 PLACES	± 0.1																
							2 PLACES	± 0.2																
					1 PLACE	± 0.2																		
					0 PLACES ± 0.2																			
					DRWN BY FSATO DATE 2015/04/30																			
					CHK'D BY KTAKAHASHI DATE 2015/06/30				PRODUCT CUSTOMER DRAWING <table><tr><td>SERIES</td><td>MATERIAL NUMBER</td><td colspan="2">CUSTOMER</td></tr><tr><td>505110</td><td>SEE SHEET 2</td><td colspan="2">GENERAL</td></tr></table>				SERIES	MATERIAL NUMBER	CUSTOMER		505110	SEE SHEET 2	GENERAL					
SERIES	MATERIAL NUMBER	CUSTOMER																						
505110	SEE SHEET 2	GENERAL																						
APPR BY DATE				DRAWING SIZE A3		THIRD ANGLE PROJECTION 		DOCUMENT NUMBER 5051100001		DOC TYPE PSD		DOC PART 000		SHEET NUMBER 1 OF 2										
A		REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																				



9 8 7 6 5 4 3 2 1

引き出し方向
PULL OUT
DIRECTION

トップテープ
TOP TAPE



SECT. X-X








SECT. Y-Y

11.5	24	29.4	25.4	10.4	14.4	15.5	5051101992	19
				9.9	13.9	15.0	5051101892	18
				9.4	13.4	14.5	5051101792	17
				8.9	12.9	14.0	5051101692	16
				8.4	12.4	13.5	5051101592	15
				7.9	11.9	13.0	5051101492	14
				7.4	11.4	12.5	5051101392	13
				6.9	10.9	12.0	5051101292	12
				6.4	10.4	11.5	5051101192	11
				5.9	9.9	11.0	5051101092	10
				5.4	9.4	10.5	5051100992	9
				4.9	8.9	10.0	5051100892	8
7.5	16	21.4	17.4	4.4	8.4	9.5	5051100792	7
				3.9	7.9	9.0	5051100692	6
				3.4	7.4	8.5	5051100592	5
H	F	E	D	C	B	A	EMBOSSED PACKAGE	Ckt
CONNECTION NO. 505110**12							オーダー番号 ORDER NO.	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC DESCRIPTION EC NO: 100528 DRWN: NKONDO CHK'D: KTAKAHASHI APPR: KMORIKAWA 2015/06/30 2015/06/30 2015/06/30				QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex					
							MM		2:1							
				 = 0			ANGULAR TOL ± 1.0 °		DRWN BY		DATE		0.5 FPC CONN ZIF E/O 2 CONT TYPE EMB PKG			
				 = 0					FSATO		2015/04/30					
				 = 0			4 PLACES	± 0.05	CHK'D BY		DATE					
 = 0	3 PLACES	± 0.1	KTAKAHASHI		2015/06/30		PRODUCT CUSTOMER DRAWING									
 = 0	2 PLACES	± 0.2	APPR BY		DATE											
 = 0	1 PLACE	± 0.2	DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER					
 = 0	0 PLACES	± 0.2					505110		SEE CHART		GENERAL					
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER					
 = 0							5051100001		PSD	000	2 OF 2					
 = 0																



12.6	9.0	14.2	5051101992	19
12.1	8.5	13.7	5051101892	18
11.6	8.0	13.2	5051101792	17
11.1	7.5	12.7	5051101692	16
10.6	7.0	12.2	5051101592	15
10.1	6.5	11.7	5051101492	14
9.6	6.0	11.2	5051101392	13
9.1	5.5	10.7	5051101292	12
8.6	5.0	10.2	5051101192	11
8.1	4.5	9.7	5051101092	10
7.6	4.0	9.2	5051100992	9
7.1	3.5	8.7	5051100892	8
6.6	3.0	8.2	5051100792	7
6.1	2.5	7.7	5051100692	6
5.6	2.0	7.2	5051100592	5
5.1	1.5	6.7	5051100492	4
C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	Ckt

CONNECTOR SERIES NO. 505110** 12

REVISED

EC NO: 117930
DRWN: JASANUMA
CHK'D: YKOBAYASHI02
APPR: TKUSUHARA01

2017/06/09
2017/06/12
2017/06/12

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ± 0.05

3 PLACES ± 0.1

2 PLACES ± 0.2

1 PLACE ± 0.2

0 PLACES ± 0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS

MM

DRWN BY

FSATO

CHK'D BY

KTAKAHASHI

APPR BY

KMORIKAWA

DRAWING SIZE

A3

SCALE

8:1

DATE

2015/04/30

DATE

2015/06/30

DATE

2015/06/30

THIRD ANGLE PROJECTION

molex

0.5 FPC CONN ZIF E/O 2CONT TYPE HSG ASSY

PRODUCT CUSTOMER DRAWING

SERIES

505110

MATERIAL NUMBER

SEE CHART

CUSTOMER

GENERAL

DOCUMENT NUMBER

5051101001

DOC TYPE

PSD

DOC PART

000

SHEET NUMBER

1 OF 3

