

HALOPAR 30 75 W 230 V 30° E27

OSRAM HALOPAR 30 | Halogen lamps with parabolic reflector PAR 30, with screw base



- General illumination
- Workplace lighting
- Kitchen lighting
- Object lighting
- Accent lighting
- Shops
- Restaurants, hotels and similar prestigious applications

Product benefits

- Brilliant accent light
- With whole glass reflector for brilliant lighting effects
- Instant 100 % light, no warm-up time
- Approved for use in open luminaires (to IEC 60598-1)
- Contains no mercury, can be thrown away with normal household waste
- UV filter

Product features

- Average life: 2,000 h
- 100 % dimmable
- Perfect color rendering (R_a : 100)
- Color temperature: 2,900 K



Technical data

Electrical data


Rated wattage	75 W
Nominal wattage	75 W
Nominal voltage	230 V
Rated power factor λ	1.00

Light technical data

Luminous intensity	2200 cd
Beam angle	30 °
Rated color temperature	2900 K
Rated color rendering index Ra	100
Rated starting time	0.0 s
Rated warm-up time (60 %)	0 s
Lumen main.fact.at end of nom.life time	0.70

Dimensions & weight

Length	90.5 mm
Overall length	90.5 mm
Diameter	97.0 mm
Outer bulb	PAR95



Product line drawing with letters



E27
IEC 7004-21

Base



E 27

Base

Colors & materials

Rated lamp mercury content	0.0 mg
Mercury-free	Yes


Lifespan

Nominal lamp life time	2000 h
Rated lamp life time	2000 h
Rated number of switching cycles	1000000 ¹⁾


¹⁾ At 1 s on / 1 s off

Additional product data


Base (standard designation)	E27
Footnote used only for product	Not suitable for outdoor use or damp conditions



Luminous intensity distribution



Luminous intensity distribution



64845 FL

64841 FL: +/- 8%

*Luminous intensity distribution***Capabilities**

Dimmable	Yes
Burning position	Any

Country specific categorizations

ILCOS	HAGS/UB-75-240-E27-97/30
Order reference	64841 FL

Logistical Data

Product code	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Gross weight	Volume
4050300338484	Folding carton box 1	90 mm x 90 mm x 106 mm	206.00 g	0.86 dm ³
4050300338491	Shipping carton box 15	336 mm x 172 mm x 521 mm	3540.00 g	30.11 dm ³

References / Links

For light distribution curves see

► www.osram.com

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.