

DC-11402

MINI USB-KVM switch, with audio support - 1User, 2PCS



Features

- Control two PCs with one USB keyboard, one USB mouse and one monitor
- Simple installation: No additional software required
- PC selection via hotkey
- LED indicator for monitoring working status of PC and Audio
- Excellent video quality-up to 2048 x 1536, @85HZ
- Support DDC, DDC2, DDC2B, DDC2AB
- Audio support
- Hot plug and play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan (5,10,20,40,60 sec options)
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.2m
- Support Window 98SE/ME/2000/2003 server/XP/VISTA, Sun Micro , Mac , Linux

System requirements

- **Computer:** USB port, VGA port
- **Operating System:** 98SE/ME/2000/2003 server/XP/VISTA, Sun Micro , Mac , Linux

Package Contents

- 2 port MINI USB-KVM switch
- User manual
- Quick installation guide

Specification		
Number Of Computers Controlled		2
Selection Method		USB Keyboard Hot Key, Push Button
USB Versions supported		1.1
LEDs		Red for PC Selection Green for PC ON-Line Selection
PC Connectors	USB	2 x Type A USB Connectors
	Video	2 x HDB-15 male
	Speaker	2 x Stereo speaker plugs
	Microphone	2 x Mono microphone plugs
	KVM Body	1 x DVI 24+5 Connector (male)
Console Ports	Keyboard / Mouse	2 x Type A USB Connectors (female)
	Video	1 x HDB-15 female
	Speaker	1 x Stereo speaker jack
	Microphone	1 x Mono microphone jack
	HOST	1 x DVI 24+5 Connector (female)
Auto-Scan Interval		5,10,20,40,60 Seconds
DDC, DDC2 monitor		Yes (Max. Resolution: 2048x1536)@85Hz
Hot Swappable		Yes
Operating systems supported		Windows 98SE/ME/2000/XP/2003 Server
		Sun Micro, Mac, Linux
Device driver		No
Power		By PC USB power
Cable Length		1.20 Meter
Dimensions (LxWxH)		65 x 85 x 25 (mm)
Unit Weight		450 g
Housing material		Plastic
Operating Temperature		32~ 122°F (0~ 50°C)
Humidity		0%~80%RH