



Shrink-Kon®

HSB63

General purpose, flexible heat shrink tubing for the protection, insulation and bundling of cables.

T&B Catalog Number:

HSB63

EAN Number:

05414363104452

UPC Number:

78621053851

Description:

PLG thin wall flexible heat shrink tubing, with expanded diameter 1.6 mm, black, shrink ratio 2:1, length 12 m

Technical Information

Tubing Family	PLG
Wall Thickness	thin
Shrink Ratio	2:1
Tube Characteristics	single wall
Material	PE crosslinked polyolefin
Temperature Range	-55°C to +125°C
Shrink Temperature	> +110°C
IP Rating	IP60
Flammability Rating	self-extinguishing
Colour	black
Silicone free	yes
Lead/Cadmium free	yes
Dielectric Strength	20 KV/mm
Chemical Resistance	good

Ordering Information

Expanded Diameter as Supplied (inch)	1/16
Expanded Diameter as Supplied (mm)	1.6
Fully Recovered Diameter (mm)	0.8
Wall Thickness before Shrinking (mm)	0.2
Wall Thickness after Shrinking (mm)	0.4
Length (m)	12
Packaging Type	Dispenser box