

**Series 801 "Mighty Mouse"
Protective Covers
667-217 & 667-218**





**Series 801
Heavy Duty**

How to Order Series 801 Protective Covers

Series 801 Double-Start Protective Covers are available with a variety of lanyard options and ring terminal sizes.

A flourosilicone gasket provides environmental sealing.

How To Order 801 Series Protective Covers

Series	Shell Material / Finish	Attachment Type		Attachment Ring Diameter			Attachment Length in Inches
				D: Aperture	E: Overall		
667-217 Protective Cover for Use With Series 801 Plugs 	C Aluminum, with Black Anodized Finish	D —Bead Chain Stainless Steel	5	01 – .125 (3.2)	.300 (7.6)	Example 6 = Six Inch Attachment Length	
	M Aluminum, with Electroless Nickel Finish	F —Wire Rope Nylon Jacket	6	02 – .140 (3.6)	.300 (7.6)		
	NF Aluminum, with Olive Drab Cadmium Finish	G —Nylon Rope, Black	7	03 – .167 (4.2)	.300 (7.6)		
			8	04 – .182 (4.6)	.300 (7.6)		
			9	05 – .191 (4.9)	.300 (7.6)		
			10	06 – .197 (5.0)	.300 (7.6)		
			13	07 – .391 (9.9)	.770 (19.6)		
			16	08 – .516 (12.1)	.890 (22.6)		
			17	09 – .583 (14.8)	.810 (20.6)		
				10 – .766 (19.5)	1.140 (29.0)		
667-218 Protective Cover for Use With Series 801 Receptacles 	ZN Aluminum, with Olive Drab Zinc-Nickel Finish	N —No Attachment	10	11 – .896 (22.2)	1.180 (30.0)		
	ZNU Aluminum, with Black Zinc-Nickel Finish	R —Wire Rope PVC Jacket	13	12 – 1.016 (25.8)	1.390 (35.3)		
	Z1 Stainless Steel, with Passivated Finish	S —Sash Chain Stainless Steel	16	13 – 1.141 (29.0)	1.520 (38.6)		
		T —Wire Rope, No Jacket	17	14 – .385 (9.8)	.510 (13.0)		
		U —Wire Rope, Polyurethane Jacket		15 – .445 (11.3)	.570 (14.5)		
				16 – .570 (14.5)	.690 (17.5)		
				17 – .635 (16.1)	.760 (19.3)		
				18 – .695 (17.7)	.820 (20.8)		
				19 – .885 (22.5)	1.010 (25.7)		
				20 – 1.070 (27.2)	1.200 (30.5)		
				21 – 1.135 (28.8)	1.250 (31.8)		

Part Number Example

667-218

—NF

—G


6

01


—3

Series 801 Protective Cover Dimensions

Series 801 Protective Cover Dimensions



667-217 Plug Cover



667-218 Receptacle Cover

Series 801 Protective Cover Dimensions

Shell Size	Ø A Max.	Ø B	Ø C
5	.465 (11.8)	.3125-.05P-.1L-2A	.3125-.05P-.1L-2B
6	.525 (13.3)	.375-.05P-.1L-2A	.375-.05P-.1L-2B
7	.590 (15.0)	.4375-.05P-.1L-2A	.4375-.05P-.1L-2B
9	.715 (18.2)	.5625-.05P-.1L-2A	.5625-.05P-.1L-2B
13	.965 (24.5)	.8125-.1P-.2L-2A	.8125-.1P-.2L-2B
16	1.150 (29.2)	1.000-.1P-.2L-2A	1.000-.1P-.2L-2B
17	1.062 (27.0)	1.062-.1P-.2L-2A	1.062-.1P-.2L-2B

Solid Ring: Dash Number 07 Thru 12

