

0359 0359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0358 0358-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0360 0360-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0343 0343-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole
0356 0356-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel. Order as: 0356-0-57-XX-34-XX-10-0	6659 6659-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole	0347 0347-0-15-XX-34-XX-10-0 Solder mount in .120 min. mounting hole	0329 0329-0-15-XX-34-XX-10-0 Solder mount in .075 min. mounting hole. "knock out" bottom.
0814 0814-0-15-XX-34-XX-04-0 Solder mount in .082 min. mounting hole	5059 5059-0-15-XX-34-XX-04-0 Press-fit in .090 mounting hole	8360 8360-0-15-XX-34-XX-10-0 Press-fit in .087 mounting hole	9359 9359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
 LENGTHS: ±.005
 DIAMETERS: ±.002
 ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 27 30μ" GOLD OVER NICKEL (RoHS)

CONTACT

#34 CONTACT (DATA ON PAGE 224)