

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0755810002](#)
Status: **Active**
Overview: [ipass](#)
Description: 0.80mm Pitch, iPass™ Stacked I/O, External Application, Integrated Cage and Connector Assembly, Right Angle, Press-Fit, 136 Circuit, 0.76µm Gold (Au) Plating

Documents:

[3D Model](#) [Product Specification PS-75586-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	75581
Application	Wire-to-Board
Component Type	Cage Assembly, Receptacle
Overview	ipass
Product Name	iPass™, PCI Express*
Type	N/A

Physical

Circuits (Loaded)	136
Circuits (maximum)	136
Color - Resin	Black
Durability (mating cycles max)	250
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Orientation	Right Angle
PC Tail Length	2.08mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Wire Insulation Diameter	N/A
Wire Size AWG	N/A


Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	N/A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Product Specification	PS-75586-001
Sales Drawing	SD-75581-001



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[75581](#)Series

Mates With

[74547](#) iPass™ Cable Assembly

Use With

[75586](#) Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Press-In Tool for	0622030400
iPass™ 16X PCIE	
iPass™ 16X PCIE	0622030410
Removal Tool	

This document was generated on 02/08/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION