


Metric Pan head machine screws - Slotted



DIN 85
BS 4183
ISO 1580

Materials/Finishes:

Steel 4.8/Zinc & clear
Stainless steel/Self colour
Brass/Self colour

Dimensions

Thread (d)	M2	M2.5	M3	M3.5	M4	M5	M6	M8
D max	4	5	6	7	8	10	12	16
H max	1.3	1.5	1.8	2.1	2.4	3	3.6	4.8
w (slot width) nom	0.7	0.8	1	1.2	1.4	1.5	1.8	2.2
t (slot depth) nom	0.5	0.6	0.7	0.8	1	1.2	1.4	1.9

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

Preferred lengths

		Thread (d)							
		M2	M2.5	M3	M3.5	M4	M5	M6	M8
Length (L)	4								
	5			ST A2					
	6		ST A2	ST A2 BR		ST A2			
	8		ST A2	ST A2 BR		ST A2 BR	ST A2 BR		
	10		ST A2	ST A2 BR		ST A2 BR	ST A2 BR	ST A2	
	12		ST A2	ST A2 BR		ST A2 BR	ST A2 BR	ST A2 BR	
	16			ST A2 BR		ST A2 BR	ST A2 BR	ST A2 BR	
	20			ST A2 BR		ST A2 BR	ST A2 BR	ST A2 BR	
	25			ST BR		ST A2 BR	ST A2 BR	ST A2 BR	
	30			ST BR		ST A2 BR	ST A2 BR	ST A2 BR	
	35			ST		ST BR	ST A2 BR	ST A2 BR	
	40			ST		ST BR	ST BR	ST BR	
	45								

	50								
	60								
	65								

ST - Steel, Zinc & clear - other finishes often available
A2 - A2 Stainless steel, Self colour
BR - Brass, Self colour