



Connectors, reducers and couplers

• HG-Y Y-Connector, IP66

Features and Benefits

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus



HelaGuard HG-Y, Y-Connector, IP66.

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-25801	HG16-Y13	16	13	5
166-25802	HG21-Y16	21	16	3
166-25803	HG28-Y21	28	21	3
166-25804	HG34-Y28	34	28	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Operating Temperature	-50 °C to +135 °C
Flammability	UL94 V2



• HGL-Y Y-Connector, IP68

Fulfills IP66, IP67, IP68 and IP69k.

Features and Benefits

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus



HelaGuard HGL-Y, Y-Connector with conduit seals.

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-25901	HGL16-Y13	16	13	5
166-25902	HGL21-Y16	21	16	3
166-25903	HGL28-Y21	28	21	3
166-25904	HGL34-Y28	34	28	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



Please note! Not all products listed on this page may have this approval.
For product specific approvals please refer to the Appendix.