



Bottom View of Assembly





SECTION A-A (Side View Inside Assembly)




SECTION B-B (Inside of Bottom Cover)


End View of Assembly




Front/Rear Panel (Dashed Line Indicates Viewing Area)



Maximum P.C. Board Size



Instrument (1598J)



NOTE

Purchased assembly includes top and bottom cover, front and end aluminum panels (type 5005H32, SPV coating on one side), 2 cover screws, and 4 rubber feet.

PART NUMBERS

1598J- Polystyrene (UL94-HB)		
Grey Enclosure with Aluminum Panels	Grey Enclosure with Black Plastic Panels	Black EMI/RFI Shielded
1598JSGY	1598JSGYPBK	--
1598J - Flame Retardant ABS (UL94-VO)		
Black Enclosure with Aluminum Panels	Grey Enclosure with Aluminum Panels	Black EMI/RFI Shielded
1598JBK	1598JGY	1598RJBK
Accessories		
Black Plastic Panels (Optional)		Rubber Feet (Pkg 24)
1598PLJBK		1421T3
For 1598 Polystyrene Cover Screws (Pkg 100) [#4 x 5/8" (15.9mm)]	For 1598 FR-ABS Cover Screws (Pkg 100) [M3 - 0.5" x 10mm]	Both Models P.C. Board Screws (Pkg 100) [#6 x 1/4" (6.4mm)]
1598TS100	1591MS100	1598ATS100



www.hammondmfg.com