


Z1 SMA1 ... Z1 SMA100 (1W)



Surface mount diode

Zener silicon diodes

Z1 SMA1...Z1 SMA100 (1W)

**Maximum Power
Dissipation: 1 W**

Nominal Z-voltage: 1 to 100 V

Features

- Max. solder temperature: 260°C
- Plastic material has UL classification 94V-0
- Standard Zener voltage tolerance is graded to the international E 24 (5%) standard. Other voltage tolerances and higher Zener voltages on request.

Mechanical Data

- Plastic case SMA / DO-214AC
- Weight approx.: 0.07 g
- Terminals: plated terminals solderable per MIL-STD-750
- Mounting position: any
- Standard packaging: 7500 pieces per reel

¹⁾ Mounted on P.C. board with 25 mm² copper pads at each terminal

²⁾ Tested with pulses

³⁾ The Z1SMA1 is a diode operated in forward. Hence, the index of all parameters should be "F" instead of "Z". The cathode, indicated by a white band is to be connected to the negative pole.

Absolute Maximum Ratings T_C = 25 °C, unless otherwise specified			
Symbol	Conditions	Values	Units
P _{tot}	Power dissipation, T _A = 50 °C ¹⁾	1	W
P _{ZSM}	Non repetitive peak power dissipation, t < ms		W
R _{thA}	Max. thermal resistance junction to ambient	70	K/W
R _{thT}	Max. thermal resistance junction to terminal	30	K/W
T _j	Operating junction temperature	- 50 ... + 150	°C
T _s	Storage temperature	- 50 ... + 175	°C

Type	Zener Voltage ²⁾ V _Z @I _{ZT}		Test curr. I _{ZT} mA	Dyn. Resistance Z _{ZT} @I _{ZT} Ω	Temp. Coeffiz. of V _Z a _{VZ} 10 ⁻⁴ /°C	I _R V _R μA V		Z- curr. ¹⁾ T _A = 50 °C I _{Zmax} mA
	V _{Zmin} V	V _{Zmax} V						
Z1SMA1 ³⁾	0,71	0,82	5	6,5 (<8)	- 26 ... - 23	1	-	500
Z1SMA10	9,4	10,6	5	5,2 (<15)	+ 2 ... + 7	1	> 7,5	94
Z1SMA11	10,4	11,6	5	6 (<20)	+ 3 ... + 7	1	> 8,5	86
Z1SMA12	11,4	12,7	5	7 (<20)	+ 4 ... + 7	1	> 9	79
Z1SMA13	12,4	14,1	5	9 (<25)	+ 5 ... + 8	1	> 10	71
Z1SMA15	13,8	15,6	5	11 (<30)	+ 5 ... + 8	1	> 11	64
Z1SMA16	15,3	17,1	5	13 (<40)	+ 5 ... + 9	1	> 12	58
Z1SMA18	16,8	19,1	5	18 (<50)	+ 6 ... + 9	1	> 14	52
Z1SMA20	18,8	21,2	5	20 (<50)	+ 7 ... + 9	1	> 15	47
Z1SMA22	20,8	23,3	5	25 (<55)	+ 7 ... + 9	1	> 17	43
Z1SMA24	22,8	25,6	5	28 (<80)	+ 7 ... + 9,5	1	> 18	39
Z1SMA27	25,1	28,9	5	30 (<80)	+ 8 ... + 9,5	1	> 20	35
Z1SMA30	28	32	5	35 (<80)	+ 8 ... + 9,5	1	> 22,5	31
Z1SMA33	31	35	5	40 (<80)	+ 8 ... + 10	1	> 25	29
Z1SMA36	34	38	5	40 (<90)	+ 8 ... + 10	1	> 27	26
Z1SMA39	37	41	5	50 (<90)	+ 8 ... + 10	1	> 29	24
Z1SMA43	40	46	5	60 (<100)	+ 8 ... + 10	1	> 32	22
Z1SMA47	44	50	5	70 (<100)	+ 8 ... + 10	1	> 35	20
Z1SMA51	48	54	5	70 (<100)	+ 8 ... + 10	1	> 38	19
Z1SMA56	52	60	5	70 (<100)	+ 9 ... + 11	1	> 42	17
Z1SMA62	58	66	5	80 (<110)	+ 9 ... + 11	1	> 47	15
Z1SMA68	64	72	5	90 (<140)	+ 9 ... + 12	1	> 51	14
Z1SMA75	70	79	5	95 (<150)	+ 9 ... + 12	1	> 56	13
Z1SMA82	77	88	5	100(<170)	+ 9 ... + 12	1	> 62	11
Z1SMA91	85	96	5	130(<200)	+ 10 ... + 12	1	> 68	10
Z1SMA100	94	106	5	200(<300)	+ 10 ... + 12	1	> 75	9