

0,635 mm, Sandwich

art. no.	dim. [mm]		art. no.	dim. [mm]	
	A	L		A	L
SL 13 071 ...	7.10	21.40	SL 13 235 ...	23.50	37.80
SL 13 097 ...	9.70	24.00	SL 13 265 ...	26.50	40.80
SL 13 122 ...	12.20	26.50	SL 13 310 ...	31.00	45.30
SL 13 147 ...	14.70	29.00	SL 13 365 ...	36.50	50.80
SL 13 187 ...	18.70	33.00			
art. no.	dim. [mm]		art. no.	dim. [mm]	
	A	L		A	L
SL 14 071 ...	7.10	21.40	SL 14 235 ...	23.50	37.80
SL 14 097 ...	9.70	24.00	SL 14 265 ...	26.50	40.80
SL 14 122 ...	12.20	26.50	SL 14 310 ...	31.00	45.30
SL 14 147 ...	14.70	29.00	SL 14 365 ...	36.50	50.80
SL 14 187 ...	18.70	33.00			
please indicate:					
... no. of contacts		... surface			
one row 1-36		S =selective gold-plated			
two rows 2-72		G=gold-plated			
		Z =tin-plated			

"S" selective gold-plated to 33.0 mm pin length

For interconnections of stacked PCBs. The male headers SL 13 and SL 14 are used to connect BL 11 (SL 13 ...) and BL 12 (SL 14 ...). Suitable for PCBs 1.5 mm - 3.0 mm thick.
V-notches permit breaking! Therefore any required number of contacts is available. Every pin length is available on request.

Female headers 2.54 solder
Fem. head. 2.54 solder, put through
Female headers 2.54 SMD
IDC-connectors

→ G 27
→ G 28
→ G 41 - 44
→ H 1 - 14

Jumpers
Special male & female headers
High-prec. fem. headers 2.54 sold.
Technical data

→ G 72 - 73
→ G 19
→ G 30 - 33
→ G 72 - 76